

GVSBPSU150KH

Maintenance Bypass Panel, single unit, 150kW
400V wallmount, for Galaxy VS and Easy UPS
3M



Overview

Presentation	Maintenance bypass cabinet for complete isolation of the UPS during service operations.
Lead time	Usually Ships within 2 Weeks

Main

Main Input Voltage	3 phase
--------------------	---------

Physical

Height	31.50 in (80 cm)
Width	23.62 in (60 cm)
Depth	11.02 in (28 cm)
Net Weight	105.82 lb(US) (48 kg)

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...3000 ft
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature for Storage	-13...131 °F (-25...55 °C)
Storage Relative Humidity	Non-condensing 0...95 %

Ordering and shipping details

GTIN	731304405658
Package weight(Lbs)	105.82 lb(US) (48 kg)

Packing Units

Package 1 Height	31.50 in (80 cm)
Package 1 width	23.62 in (60 cm)
Package 1 Length	11.02 in (28 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.