

# Product data sheet

## Characteristics

# AP6020A

Rack PDU, Basic, 0U/1U, 100-240V/20A, 220-240V/16A, (13) C13



### Overview

Presentation	Reliable rack power distribution designed to increase manageability and efficiency in the data center. The output and input connections are (13) C13. Real-time remote monitoring of connected loads. User-defined alarms warn IT and data center managers of potential circuit overloads to prevent accidental power loss to critical equipment.
Lead time	Usually in Stock

### Main

Main Input Voltage	100 V 120 V 200 V 208 V 230 V 240 V
Input Connection Type	IEC 60320 C20
Number of rack unit	1U
Provided Equipment	Installation guide Safety guide

### Physical

Color	Black
Height	15.28 in (38.8 cm)
Width	1.73 in (4.4 cm)
Depth	3.66 in (9.3 cm)
Net Weight	3.31 lb(US) (1.5 kg)
Mounting Location	Front Rear
Mounting preference	Lower
Mounting Mode	Not rack-mountable
USB compatible	No

### Input

Line Rated Current	16 A
Acceptable Input Voltage	100...240 V
Max line current	20 A
Input current limits	20 A
Load Capacity	3300 VA
Input Frequency	50/60 Hz

### Output

Number of power socket outlets	13 IEC 60320 C13
--------------------------------	------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Conformance

Product Certifications	CUL Listed CE EAC IRAM PSE UL Listed VDE
------------------------	--

## Ordering and shipping details

GTIN	731304327806
Package weight(Lbs)	4.45 lb(US) (2.02 kg)

## Packing Units

Package 1 Height	17.17 in (43.6 cm)
Package 1 width	8.27 in (21 cm)
Package 1 Length	2.99 in (7.6 cm)
SCC14	10731304327803
Number of Units in Package 3	100

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------