

Product data sheet

Characteristics

HMIG5UL8B

Base unit, Harmony GTU, Open BOX for Univ Panel, EcoStruxure Machine SCADA Expert v8.1+SP2 pre installed



Main

Range of Product	Harmony GTU
Product or Component Type	Base unit
Device short name	Open Box
Range Compatibility	Harmony GTU Allen-Bradley ABB Mitsubishi Omron Siemens
[Us] rated supply voltage	12...24 V DC power supply

Complementary

Integrated connection type	Ethernet TCP/IP 2 RJ45 COM1 serial link RJ45 RS485 110...115200 bit/s COM2 serial link SUB-D 9 RS232C/RS422/RS485 110...115200 bit/s Auxiliary port terminal block Expansion unit fieldbus card USB 2.0 port mini B USB DVI-D video port DVI-D Microphone mini-jack USB 2.0 port 3 USB type A
Communication port protocol	Modbus Modbus TCP/IP Uni-Telway
Operating system	Windows Embedded 7
Software package	Internet Explorer EcoStruxure machine SCADA expert trial version .NET framework 4.0 Adobe PDF reader Multimedia player Office reader VNC client/server
Processor name	Intel X86 1.33 GHz
Data storage equipment	32 GB CFast card
Port Ethernet	10BASE-T/100BASE-TX/1000BASE-T
Memory description	512 kB NVRAM backup memory 2 GB RAM internal
Number of slots	1 slot(s) for SD card 2 slot(s) for CFast card
Realtime clock	Built-in
Local signalling	, multi-colour LED status
Type of cooling	Natural convection
Width	7.40 in (188 mm)
Height	5.16 in (131 mm)
Depth	1.77 in (45 mm)
Net Weight	1.98 lb (US) (0.9 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	CSA C22.2 No 142 ANSI/ISA 12-12-01 UL 508 Class I division 2 CSA C22.2 No 213 IEC 61132-2
Product certifications	CE CULus ATEX IEC-Ex RCM GL KC CUL EAC ABS BV CCS DNV LR RINA
Resistance to fast transients	1 KV IEC 61000-4-4 signal ports) 2 KV IEC 61000-4-4 power ports)
Resistance to electrostatic discharge	6 KV contact discharge EN/IEC 61000-4-2 level 3 8 KV air discharge EN/IEC 61000-4-2 level 3
Ambient air temperature for operation	32...140 °F (0...60 °C)
Ambient air temperature for storage	-4...140 °F (-20...60 °C)
Pollution degree	2 EN 61131-2 Ed.3
Relative Humidity	10...90 % non-condensing
Operating altitude	6561.68 ft (2000 m)
Vibration resistance	3.5 mm constant amplitude 5...9 Hz) EN/IEC 61131-2 9.8 m/s ² 9...150 Hz) EN/IEC 61131-2
Shock resistance	147 m/s ² EN/IEC 61131-2
Electromagnetic compatibility	Electrostatic discharge immunity testlevel 3 EN/IEC 61000-4-2

Ordering and shipping details

Category	22567-MAGELIS HMI GTU
Discount Schedule	MC2
GTIN	3606489818517
Returnability	No

Packing Units


Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.31 in (13.5 cm)
Package 1 Width	8.27 in (21.0 cm)
Package 1 Length	10.24 in (26.0 cm)
Package 1 Weight	2.65 lb(US) (1.202 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Dimensions

External Dimensions



1 Front

2 Left

3 Bottom