

# Product data sheet

## Characteristics

# AP8659NA3

## Rack PDU 2G, Metered by Outlet with Switching, ZeroU, 20A, 208V, (21) C13 & (3) C19



### Overview

#### Presentation

APC Metered by Outlet with Switching Rack Power Distribution Units (PDUs) enable advanced, user-customizable power control and individual outlet power metering. Remote outlet level controls allow power on/off functionality for power recycling to reboot locked-up equipment and to avoid unauthorized use of individual outlets. Power sequencing delays allow users to define the order in which to power up or down attached equipment. Avoid circuit overload during power recovery and extend uptime of critical equipment by prioritizing the load shedding. Current metering provides real-time remote monitoring of connected loads. Switched Rack PDUs include real power monitoring, a temperature/humidity sensor port, and locking IEC receptacles. User-defined alarms warn of potential circuit overloads before critical IT failures occur. Users can access, configure, and control Switched rack PDUs through secure Web, SNMP, or Telnet Interfaces and is complimented by APC Centralized Management platforms using InfraStruxure Central, Capacity Manager and Change Manager.

#### Lead time

Usually in Stock

### Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	208 V
Plug standard	NEMA L6-20P
Number of rack unit	0U
Cable length	9.84 ft (3.00 m)
Provided Equipment	CAN Port Terminator Installation guide Locking input power cord Rack Mounting brackets Safety guide Serial configuration cable

### Physical

Color	Black
Height	72.01 in (182.9 cm)
Width	2.20 in (5.6 cm)
Depth	2.01 in (5.1 cm)
Net Weight	14.93 lb(US) (6.77 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Not rack-mountable

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Input

Line Rated Current	16 A
Acceptable Input Voltage	100...240 V
Input current limits	20 A
Load Capacity	3300 VA
Input Frequency	50/60 Hz

## Output

Number of power socket outlets	21 IEC 60320 C13 3 IEC 60320 C19
--------------------------------	-------------------------------------

## Conformance

Product Certifications	UL Listed VCCI Class A VDE
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC Part 15 class A ICES-003

## Environmental

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Ordering and shipping details

GTIN	731304299523
Package weight(Lbs)	19.95 lb(US) (9.05 kg)

## Packing Units

Package 1 Height	80.24 in (203.8 cm)
Package 1 width	6.38 in (16.2 cm)
Package 1 Length	4.61 in (11.7 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------