



Overview

Presentation	APC Switched Rack Power Distribution Units (PDUs) enable advanced, user-customizable power control and active monitoring. Remote outlet level controls allow power on/off functionality for power recycling to remotely reboot equipment and restrict unauthorized use of individual outlets. Power sequencing delays allow users to define the order in which to power up or down attached equipment. Avoid circuit overload during power recovery and extend uptime of critical equipment by prioritizing the load shedding. Current metering provides real-time remote monitoring of connected loads. Switched Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and low profile circuit breakers. User-defined alarms warn of potential circuit overloads before critical IT failures occur. Users can access, configure, and control Switched Rack PDUs through secure Web, SNMP, or Telnet Interfaces and is complimented by APC Centralized Management platforms using InfraStruxure Central, Capacity Manager and Change Manager.
Lead time	Usually in Stock

Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	200 V 208 V 230 V 240 V
Plug standard	NEMA L6-20P
Number of rack unit	0U
Cable length	9.84 ft (3.00 m)
Number of cables	1
Provided Equipment	Installation guide Locking input power cord Rack Mounting brackets Serial configuration cable Safety guide

Physical

Color	Black
Height	38.90 in (98.8 cm)
Width	2.20 in (5.6 cm)
Depth	1.81 in (4.6 cm)
Net Weight	7.12 lb(US) (3.23 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Not rack-mountable
USB compatible	No

Input

Line Rated Current	16 A
Acceptable Input Voltage	200...240 V
Input current limits	20 A
Load Capacity	3300 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	7 IEC 60320 C13 1 IEC 60320 C19
--------------------------------	------------------------------------

Conformance

Product Certifications	CUL Listed PSE UL Listed VCCI Class A VDE
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC Part 15 class A ICES-003

Environmental

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304277125
Package weight(Lbs)	12.13 lb(US) (5.5 kg)

Packing Units

Package 1 Height	44.29 in (112.5 cm)
Package 1 width	6.50 in (16.5 cm)
Package 1 Length	4.49 in (11.4 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------