



Overview

Presentation

Ideal for retail, healthcare, educational facilities, and light industrial spaces, the low-profile APC wall mount rack offers an efficient solution for deploying hyper-converged servers and networking for edge computing applications. The rack enclosure allows longer depth equipment to be wall-mounted, up to 30 inches deep. A detachable wall bracket and optional casters (sold separately) allow the server rack to be mounted on either the wall or stand alone on the floor. A dust filter and two integrated fans allow deployment in light-industrial environments. Shock packaging is included and allows optional equipment pre-installed before shipment, speeding IT deployment. APC Smart-UPS, APC NetBotz Physical and Environmental Security, and APC EcoStruxure IT can be configured with this cabinet (sold separately). 6U Vertical wall mount cabinet, 30" mounting depth, 250lb weight capacity, 19" rack width, ships fully assembled, MERV 5/G3 dust filter and 120v integrated fans included, input connector IEC 60320 C13, 5 year APC warranty.

Lead time

Usually Ships within 2 Weeks

Main

Main Input Voltage	100 V 120 V
Plug standard	IEC 60320 C13
Number of rack unit	6U

Physical

Color	Black
Height	25.51 in (64.8 cm)
Width	13.90 in (35.3 cm)
Depth	38.11 in (96.8 cm)
Net Weight	80.01 lb(US) (36.29 kg)
Mounting Support	Wall
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Mounting position	Vertical
Maximum Mounting Depth	30.00 in (76.2 cm)
Minimum Mounting Depth	30.00 in (76.2 cm)
Rack Width	19"
Permanent permissible load	250 Lb(US) (113.40 kg) dynamic 250 lb(US) (113.40 kg) static

Input

Input Frequency	60 Hz
-----------------	-------

Conformance

Standards	UL 2416 EIA-310E
-----------	---------------------

Environmental

Air flow	220 ft ³ /min (103.83 l/s)
----------	---------------------------------------

Ordering and shipping details

GTIN	731304402022
Package weight(Lbs)	99.01 lb(US) (44.91 kg)

Packing Units

Package 1 Height	16.81 in (42.7 cm)
Package 1 width	41.89 in (106.4 cm)
Package 1 Length	28.90 in (73.4 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------