

# Product data sheet

## Characteristics

# VW3A4402

## additionnal EMC footprint filter S3 - 3-phase supply - 26 A

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

Range of product	Altivar
Product or component type	EMC input filter
Range compatibility	Altivar 71 Altivar 61
Product compatibility	ATV71PU40N4Z ATV71HU22M3 ATV71HU30N4 ATV61HU22M3 ATV71WU40N4 ATV71HU40N4 ATV61HU40M3 ATV61HU30M3 ATV61HU30N4 ATV71WU30N4 ATV61HU40N4 ATV71HU30M3 ATV71HU40M3 ATV71PU30N4Z
Product specific application	Radio interference input filter
Line Rated Current	26 A
Thermal losses	18 W 200...240 V AC ATV61/ATV71 variable speed drives 6 W 380...480 V AC ATV61/ATV71 variable speed drives
Phase	Three phase

### Complementary

Electrical connection	Terminal 6 mm <sup>2</sup> AWG 8
Tightening torque	13.27 lbf.in (1.5 N.m)
Maximum earth leakage current	8 mAat 400 V 50 Hz 4.4 mAat 400 V 50 Hz
Power supply voltage	200...240 V 380...500 V
Tolerance	10 %
Product weight	8.82 lb(US) (4 kg)

### Environment

IP degree of protection	IP20 IP41 (upper part)
Relative humidity	0...93 % conforming to IEC 68-2-3
Ambient air temperature for operation	14...122 °F (-10...50 °C)
Ambient air temperature for storage	-40...149 °F (-40...65 °C)
Operating altitude	3280.84...9842.52 ft (1000...3000 m) with current derating 1 % per 100 m
Vibration resistance	1.5 mm peak to peak (f = 3...13 Hz) conforming to IEC 60068-2-6 1 gn (f = 13...150 Hz) conforming to IEC 60068-2-6
Shock resistance	15 gn 11 ms conforming to EN/IEC 60068-2-27
Standards	EN 133200 EN/IEC 61800-3

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Ordering and shipping details

Category	22135 - ATV61-71 ACCESSORIES
Discount Schedule	CP4C
GTIN	003389118065611
Nbr. of units in pkg.	1
Package weight(Lbs)	11.26
Returnability	N
Country of origin	HU

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0640 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>


## Contractual warranty

Warranty period	18 months
-----------------	-----------

---

Dimensions

---



Dimensions in mm

a	b	c	G	H	Ø
155	324	50	130	309	4.5

Dimensions in in.


a	b	c	G	H	Ø
6.10	12.75	1.97	5.12	12.16	0.18

---

### Mounting Recommendations

---

#### Mounting the Filter Under the Drive



#### Mounting the Filter Next to the Drive

