



Overview

Presentation	Designed to increase flexibility and agility of data center power distribution through a design that does not require a raised floor.
Lead time	Usually Ships within 3 Weeks

Main

Main Input Voltage	3 phase
Main Output Voltage	120 V 208 V 3 phase
Number of cables	1
Provided Equipment	Installation guide User Manual

Physical

Color	Black
Height	80.98 in (205.7 cm)
Width	24.02 in (61 cm)
Depth	35.98 in (91.4 cm)
Net Weight	1014.13 lb(US) (460 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	60 Hz +/- 3 Hz
Max line current	72 A

Output

Maximum Total Current Draw per Phase	167 A
--------------------------------------	-------

Conformance

Standards	UL 60950
-----------	----------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...3333 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...30000 ft (0.00...9144.00 m)

Ordering and shipping details

GTIN	731304205821
Package weight(Lbs)	1036.17 lb(US) (470 kg)

Packing Units

Package 1 Height	85.98 in (218.4 cm)
Package 1 width	35.98 in (91.4 cm)
Package 1 Length	47.99 in (121.9 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------