

# Product data sheet

## Characteristics

# GVSMODBC6

## Galaxy VS Modular Battery Cabinet for up to 6 smart modular battery strings



### Overview

Presentation	Modular battery cabinet for extended runtime for UPSs with internal batteries. The cabinet is supplied without batteries, so batteries must be purchased separately. Up to six battery strings can be installed and monitored in the cabinet.
Lead time	Usually Ships within 2 Weeks

### Main

Battery Type	VRLA
Provided Equipment	Installation guide

### Physical

Color	White
Height	58.46 in (148.5 cm)
Width	20.51 in (52.1 cm)
Depth	33.35 in (84.7 cm)
Net Weight	319.67 lb(US) (145 kg)
Mounting Mode	Not rack-mountable

### Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)

### Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Enclosed battery cabinet
Battery Volt-Amp-Hour Capacity	0 VAh

### Ordering and shipping details

GTIN	731304367468
Package weight(Lbs)	451.95 lb(US) (205 kg)

### Packing Units

Package 1 Height	65.51 in (166.4 cm)
Package 1 width	25.00 in (63.5 cm)
Package 1 Length	38.98 in (99 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available