

Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------



Main

Main Input Voltage	208 V 3 phase
Main Output Voltage	208 V 208 V 3 phase
Kw Rating	10000 W
Rated power in VA	10000 VA
Number of cables	1
Provided Equipment	Installation guide

Physical

Color	Black
Height	5.20 in (13.2 cm)
Width	19.02 in (48.3 cm)
Depth	27.56 in (70 cm)
Net Weight	55.23 lb(US) (25.05 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Input

Input Frequency	60 Hz +/- 3 Hz
Efficiency at full load	177...239 V 208 V
Input Power Factor at Full Load	0.99

Output

Max Configurable Power (Watts)	10000 W
Harmonic distortion	Less than 5 % at full load
Output Frequency (sync to mains)	57...63 Hz for 60 Hz nominal sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal not synced
Crest factor	Unlimited
Topology	Double Conversion Online
Waveform Type	Sine wave

Conformance

Product Certifications	CUL Listed UL Listed
Standards	FCC Part 15 class A ISO 14001 ISO 9001 UL 60950

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...3333 ft
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...15000 ft (0.00...4572.00 m)
Acoustic level	64 dBA
Heat dissipation	2970 Btu/h

Batteries & Runtime

Included Battery Modules	0
Battery Slots Empty	0

Communications & Management

Free slots	0
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Ordering and shipping details

GTIN	731304301738
Package weight(Lbs)	61.84 lb(US) (28.05 kg)

Packing Units

Package 1 Height	8.86 in (22.5 cm)
Package 1 width	23.43 in (59.5 cm)
Package 1 Length	31.30 in (79.5 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------