

Product data sheet

Specifications

SQUARE D



Operating mechanism, flange mounted, variable depth, 200A, 600V, fuseholder, switch mechanism, 6 inch handle, NEMA 4

9422ATF12

Product availability: Stock - Normally stocked in distribution facility

Main

Range	9422T
Product	Disconnect Switch
Disconnect Type	Fusible disconnect switch

Complementary

Mounting Type	Flange rod variable depth
Current Rating	200 A
Horsepower Rating	40 hp 200 V AC 60 hp 230 V AC 125 hp 460 V AC 150 hp 575 V AC 40 hp 250 V DC
Fuse Rating	200 A 250/600 V
Handle Type	6 in handle included NEMA 1/3/3R/4 enclosures sheet steel
Fuse Type	R H K J

Environment

Certifications	CSA UL Recognized
----------------	----------------------

Ordering and shipping details

Category	US10CP121732
Discount Schedule	0CP1
GTIN	785901120292
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	9.00 in (22.86 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	12.30 in (31.242 cm)
Package 1 Length	20.50 in (52.07 cm)
Package weight(Lbs)	28.369 lb(US) (12.868 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
California proposition 65	<p>WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov</p>

Use Again

Repack and remanufacture

Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE Label	<p> The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.</p>