

Product data sheet

Specifications



Mini circuit breaker, E-Frame, 60A,
3 pole, 600Y/347VAC, 25kA max,
bolt on [TAA]

EDB36060

Product availability: Stock - Normally stocked in distribution facility

Main

Range	125 A Frame EDB-EGB-EJB
Product Type	Circuit-breaker
Device Short Name	EDB
Module Type	E-Frame
Trip Unit Rating	1800 A

Complementary

Rated Current	60 A
Maximum Operating Voltage	600Y/347 V AC
AWG Gauge	AWG 12...AWG 2/0 aluminium AWG 14...AWG 2/0 copper
Breaking Capacity	14 kA 600Y/347 V AC 18 kA 480/277 V AC 25 kA 240 V AC
Circuit Breaker Application	HACR rated
Electrical Connection	Lugs aluminium
Holding Current	630 A
Local Signalling	Trip indicator
Mounting Mode	Bolt-on
Number of Poles	3
Number of Spaces	3
Number of Spaces Required	3
Product Destination	NF panelboard
Protect Type	Short-circuit Overload
Trip Unit Technology	Thermal-magnetic
Breaking Capacity Code	D
Tightening Torque	34.5 lbf.in (3.9 N.m) 0.004...0.009 in ² (2.5...6 mm ²) (AWG 14...AWG 10) 49.6 lbf.in (5.6 N.m) 0.02...0.1 in ² (10...70 mm ²) (AWG 8...AWG 2/0)
Height	5.66 in (143.76 mm)
Width	2.94 in (74.68 mm)
Depth	4.05 in (102.87 mm)
Product Weight	4 lb(US) (1.8 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Product Certifications	cULus
Ambient Air Temperature for Operation	104 °F (40 °C)

Ordering and shipping details

Category	US10DE200931
Discount Schedule	0DE2
GTIN	785901235620
Returnability	Yes

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	5.00 in (12.700 cm)
Package 1 Width	6.50 in (16.510 cm)
Package 1 Length	9.90 in (25.146 cm)
Package weight(Lbs)	3.596 lb(US) (1.631 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	59
Environmental Disclosure	Product Environmental Profile

Use Better


Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	8781af64-acd9-485c-9a86-abcdfbd458e3
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No

Technical Illustration

Dimensions



All dimensions are approximate.
Also see technical drawings and/or documentation.