


Product data sheet

Specifications



TeSys Deca, suppressor module, diodes, 12...250V DC

LA4DC1U

Main

Range	TeSys
Device short name	LA4D
Product or component type	Suppressor module
Product compatibility	3P LP1D09...LP1D32

Complementary

Mounting mode	By screws
Suppressor technology	Flywheel diode
[Uc] control circuit voltage	24...250 V DC
Maximum peak voltage	1 Uc

Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.100 cm
Package 1 Width	2.800 cm
Package 1 Length	4.200 cm
Package 1 Weight	14.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	78
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.308 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Total lifecycle Carbon footprint	1
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant

Use Again

Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins