

Product availability: Stock - Normally stocked in distribution facility



Complementary

| | |
|---|---|
| Synchronisation time between inputs | 75 ms |
| Supply frequency | 50/60 Hz |
| Power consumption in W | <= 8 W |
| Input protection type | Internal, electronic |
| Time delay range | 0...30 s |
| [Uc] control circuit voltage | 48 V DC |
| Breaking capacity | C300: 180 VA, AC-15 (holding) relay output C300: 1800 VA, AC-15 (inrush) relay output |
| Breaking capacity | 1 A at 24 V (DC-13) time constant: 50 ms for relay output |
| Output thermal current | 2.5 A time delay outputs 5 A instantaneous outputs |
| [Ith] conventional free air thermal current | 8 A |
| Associated fuse rating | 4 A fuse type gG for time delay outputs conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200 6 A fuse type gG for instantaneous outputs conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200 |
| Minimum output current | 10 mA relay output |
| Minimum output voltage | 17 V relay output |
| Response time on input open | <= 20 ms |
| [Ui] rated insulation voltage | 300 V (degree of pollution: 2) conforming to DIN VDE 0110 part 1 300 V (degree of pollution: 2) conforming to IEC 60947-5-1 |
| [Uimp] rated impulse withstand voltage | 4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1 |
| Local signalling | 4 LEDs |
| Mounting support | 35 mm symmetrical DIN rail |
| Product weight | 0.84 lb(US) (0.38 kg) |

Environment

| | |
|---------------------------------------|--|
| Standards | EN/ISO 13850 EN/IEC 60947-5-1 EN/IEC 60204-1 |
| Product certifications | TÜV CSA UL |
| IP degree of protection | IP20 (terminals) conforming to EN/IEC 60529 IP40 (enclosure) conforming to EN/IEC 60529 |
| Ambient air temperature for operation | 14...131 °F (-10...55 °C) |
| Ambient air temperature for storage | -13...185 °F (-25...85 °C) |

Ordering and shipping details

| | |
|-----------------------|-----------------------------------|
| Category | 22477 - SAFETY MODULES (PREVENTA) |
| Discount Schedule | SAF2 |
| GTIN | 00785901853800 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 1.1200000000000001 |
| Returnability | Y |
| Country of origin | ID |

Offer Sustainability

| | |
|---------------------------|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| ----- Substance 1 | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| ----- More information | For more information go to www.p65warnings.ca.gov |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Dimensions

