

Product data sheet

Specifications



Switch body, TeSys Control, 3 poles, 40A

V2

Product availability: Stock - Normally stocked in distribution facility

Main

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	V
Product Type	Switch body

Complementary

Mounting Support	Plate Symmetrical rail
Performance Level	High performance
Number of Poles	3P
Contact Type and Composition	3 NO
Network type	AC DC
Network frequency	50/60 Hz
[Ue] IEC Rated Operational Voltage	690 V AC 50/60 Hz
IEC Rated Operational Power in W	11 kW 400...415 V AC-3) 11 kW 690 V AC-3) 15 kW 500 V AC-3) 15 kW 690 V AC-23A) 18.5 kW 500 V AC-23A) 5.5 kW 230...240 V AC-3) 7.5 kW 230...240 V AC-23A) 15 kW 400...415 V AC-23A)
[Ie] Rated Operational Current	29 A AC-23 Ue: 400 V
[ith] Conventional Free Air Thermal Current	40 A
[ithe] Conventional Enclosed Thermal Current	32 A
Making capacity (I Rms)	400 A 400 V AC-21A 400 A 400 V AC-22A 400 A 400 V AC-23A
Breaking Capacity	320 A 400 V AC-21A) 320 A 400 V AC-22A) 320 A 400 V AC-23A)
Rated Conditional Short Circuit Current	10 kA 400 V 50 A aM 10 kA 400 V 50 A gG
[Icm] Rated Short Circuit Making Capacity	1 kA 400 V at Ipeak
Intermittent duty class	30
Suitability for isolation	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Ui _{imp}] rated impulse withstand voltage	8 kV
[Icw] rated short-time withstand Rms current	480 A 400 V 1 s
Mechanical Durability	100000 cycles
Electrical Durability	100000 cycles AC-21 30000 cycles DC-1...5
IEC Terminal Connection	Power circuit screw clamp terminals 0.02 in ² (10 mm ²) solid Power circuit screw clamp terminals 0.009 in ² (6 mm ²) flexible - with cable end
Tightening Torque	Power circuit 18.6 lbf.in (2.1 N.m) screw clamp terminals
Height	2.9 in (74 mm)
Width	2.2 in (55 mm)
Depth	2.4 in (60 mm)
Product Weight	0.4 lb(US) (0.2 kg)

Environment

Standards	IEC 60947-3
Product Certifications	UL CSA GL UKCA CCC
Degree of Protection	IP20 conforming to IEC 60529
Protective Treatment	TC
Mechanical Robustness	Vibrations 10...150 Hz 1 gn) IEC 60068-2-6 Shocks 11 ms 30 Gn) IEC 60068-2-27
Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1

Ordering and shipping details

Category	US10CP121730
Discount Schedule	0CP1
GTIN	3389110551709
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	3.15 in (8.000 cm)
Package 1 Width	3.35 in (8.500 cm)
Package 1 Length	4.92 in (12.500 cm)
Package weight(Lbs)	6.173 oz (175.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	24
Package 2 Height	11.81 in (30.000 cm)

Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	10.430 lb(US) (4.731 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	192
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	102.850 lb(US) (46.652 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	31
--	----

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
--	-----

Packaging without single use plastic	Yes
--------------------------------------	-----

EU RoHS Directive	Compliant with Exemptions
-----------------------------------	---------------------------

SCIP Number	63dc4fbe-3f44-4801-881b-22a3bb8008d9
-------------	--------------------------------------

REACH Regulation	REACH Declaration
------------------	-----------------------------------

Halogen content performance	Halogen free product
-----------------------------	----------------------

PVC free	Yes
----------	-----

Use Again

Repack and remanufacture

Circularity Profile	No need of specific recycling operations
---------------------	--

Take-back	No
-----------	----

WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
------------	--

Technical Illustration

Assembly's dimensions

