

# Product data sheet

Specifications



Circuit breaker, PowerPacT B, 35A,  
1 pole, 600Y/347VAC, 14kA, I-Line,  
thermal magnetic, 80%, A

BDA160351

**Product availability: Stock - Normally stocked in distribution facility**

## Main

Range	PowerPact
Product name	PowerPact B
Device short name	BD 035
Product or Component Type	Circuit breaker
Device Application	Distribution

## Complementary

Line Rated Current	35 A
Number of Poles	1P
Control Type	Toggle
Breaking capacity code	D
Breaking capacity	25 kA 208Y/120 V AC 50/60 Hz UL 489 25 kA 240 V AC 50/60 Hz UL 489 18 kA 480Y/277 V AC 50/60 Hz UL 489 14 kA 125 V DC 50/60 Hz UL 489 10 kA 600/347 V AC 50/60 Hz UL 489
[Ue] rated operational voltage	240 V AC 50/60 Hz UL 489
Network Frequency	50/60 Hz
[Ics] rated service breaking capacity	25 kA 220...240 V AC 50/60 Hz IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV IEC 60947-2
Trip unit technology	Thermal-magnetic
Continuous current rating	80 %
[Ui] rated insulation voltage	800 V IEC 60947-2
Suitability for isolation	Yes IEC 60947-2
Utilisation category	Category A
Mechanical durability	20000 cycles IEC 947-1 Annex K ed 5.2
Electrical durability	10000 cycles IEC 947-1 Annex K ed 5.2 440 V In
Connection pitch	1.06 in (27 mm)
AWG gauge	AWG 14...AWG 2/0 aluminium/copper
Local signalling	Presence of auxiliary contacts flag green)
Mounting mode	I-Line
Electrical connection	I-Line connection, line Lugs, load

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Mounting Height</b>	1.5 in (38.1 mm)
<b>Tightening torque</b>	31.9...38.9 lbf.in (3.6...4.4 N.m) 0.004...0.009 in <sup>2</sup> (2.5...6 mm <sup>2</sup> ) (AWG 14...AWG 10) 44.3...54.9 lbf.in (5...6.2 N.m) 0.02...0.1 in <sup>2</sup> (10...70 mm <sup>2</sup> ) (AWG 8...AWG 2/0)
<b>Power wire stripping length</b>	0.8 in (20 mm)
<b>Color</b>	Gray RAL 7016)
<b>9 mm pitches</b>	3
<b>Height</b>	5.4 in (137 mm)
<b>Width</b>	1.06 in (27 mm)
<b>Depth</b>	3.5 in (89 mm)
<b>Product Weight</b>	1.4054 lb(US) (0.6375 kg)
<b>Quantity per Set</b>	Set of 1
<b>Phase connection</b>	A
<b>Circuit breaker application</b>	HACR rated

## Environment

<b>Quality labels</b>	CE
<b>Standards</b>	EN/IEC 60947-2 GB 14048.2 NMX J-266 UL 489 EN/IEC 60947-5-1 NEMA AB1 CSA C22.2 No 5
<b>Product certifications</b>	UL IEC CCC EAC CSA NOM
<b>IP degree of protection</b>	Front cover IP40 IEC 60529
<b>IK degree of protection</b>	IK07 conforming to IEC 62262
<b>Pollution degree</b>	3 IEC 60947-1
<b>Ambient Air Temperature for Operation</b>	-13...158 °F (-25...70 °C)
<b>Ambient Air Temperature for Storage</b>	-58...185 °F (-50...85 °C)
<b>Operating altitude</b>	< 6561.68 ft (2000 m) without derating 5000 m with derating

## Ordering and shipping details

<b>Category</b>	US10DE201133
<b>Discount Schedule</b>	0DE2
<b>GTIN</b>	3606481151049
<b>Returnability</b>	Yes
<b>Country of origin</b>	MX

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Nbr. of units in pkg.</b>	1
<b>Package 1 Height</b>	1.50 in (3.81 cm)

---

<b>Package 1 Width</b>	7.75 in (19.685 cm)
<b>Package 1 Length</b>	11.63 in (29.528 cm)
<b>Package weight(Lbs)</b>	17.600 oz (498.952 g)

---



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle) **64**

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **Yes**

[EU RoHS Directive](#) **Compliant with Exemptions**

REACH Regulation [REACH Declaration](#)

California proposition 65 **WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)**

Halogen content performance **Halogen free product**

PVC free **Yes**

## Use Again


### Repack and remanufacture

Take-back **No**

Technical Illustration

Dimensions

---



ALL DIMENSIONS ARE APPROXIMATE.  
ALSO REFER TO CAD, TECHNICAL DRAWINGS, AND DOCUMENTATION.