

Product data sheet

Specifications



License, EcoStruxure Operator Terminal Expert, windows runtime, single, 1 station, perpetual, digital

HMIRTWCZLSPAZZ

❗ To be discontinued on: Dec 12, 2025

❗ To be discontinued

Main

Range of product EcoStruxure Operator Terminal Expert

Product or component type License

Format Digital

Type of license Node locked license

Variant Runtime

Software version V3.5 SP1

Operating system requirement Windows 10 64 bit

System requirements 8 GB RAM
30 GB hard-drive space

User language English
Italian
Chinese
Spanish
French
German
Portuguese
Korean

Complementary


License category Perpetual

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Communication port protocol	CANopen slave Couzett Automation millenium 3 FBD Emerson Industrial Automation Modbus SIO master Control Techniques Modbus SIO master Emerson Process Management ROC Plus Ethernet Emerson Process Management ROC SIO HTTP IPsec Mitsubishi A series Ethernet Mitsubishi FX series CPU direct Mitsubishi FX series Ethernet Mitsubishi iQ-R/F series Ethernet SLMP client Mitsubishi Q series CPU direct Mitsubishi Q series QnU CPU Ethernet Mitsubishi Q/QnA series serial Modbus Organization Modbus SIO ASCII master Modbus Organization Modbus SIO master Modbus Organization Modbus SIO slave Modbus Organization Modbus TCP master Modbus Organization Modbus TCP slave Omron CS/CJ/CP series host link Omron CS/CJ/CP/NX series Ethernet Omron CS/CJ/NJ/NX series Ethernet/IP Profibus DP slave Rockwell Automation EtherNet/IP Rockwell Automation DH485 Schneider Electric Modbus SIO master Schneider Electric Modbus TCP master Schneider Electric Modbus TCP master via USB Schneider Electric Machine expert network Schneider Electric PacDrive Schneider Electric Uni-Telway Schneider Electric Zelio Logic Siemens Simatic S7 Ethernet Siemens Simatic S7 MPI direct Siemens TIA portal Ethernet websocket Rockwell Automation DF1 OPC UA Foundation OPC UA server
Previous software version	V3.5
Software function	Alarms and events Blocky script Convertors Import export with CSV, tab and period delimiter Data and operation logging Multi language development Multi language tables Object binding and properties Target binding and properties Project transfer (Ethernet, filesystem, USB cable) Recipes Screens (contents and folders) Security (levels, project, users) Project and application settings System keypad Text script Color themes Variable (arrays, binding, properties, structures) OPC UA Server Web server API
Range compatibility	Harmony GTU Harmony GTUX Harmony ST6 Harmony STM6 Harmony STO7 Harmony iPC
Hosting option	On-device
License size	Single (1 station)
Processor requirement	Intel core i3 8th generation Intel core i5 8th generation
Display resolution	320 x 240 pixels HVGA minimum 3840 x 2160 pixels 4K UHD maximum

Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features

Technical Benefits

EcoStruxure™ Operator Terminal Expert

