

Product data sheet

Specifications



Multisound siren, Harmony XVS,
white colour, 106dB, 2tones,
12...24V AC DC

XVS10BMW

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony XVS
Product or Component Type	Siren
Device short name	XVS
Color	White
Signalling type	2 tones siren
[Us] rated supply voltage	12 V AC/DC 24 V AC/DC
Noise level	106 dB continuous or intermittent tone)1 m

Complementary

Material	PC: body
Product Weight	1.8 lb(US) (0.8 kg)
Marking	CE
[Uiimp] rated impulse withstand voltage	0.8 kV
Current consumption	300 mA 24 V 500 mA
Clamping Connection Capacity	<= 1 x 1.5 mm ²
Electrical connection	Cable 0.3...0.3 in (6.5...8.5 mm)
Width	4.5 in (114 mm)
Height	4.5 in (114 mm)
Depth	6.03 in (153.2 mm)

Environment

Standards	IEC 60947-1 IEC 60947-5-1
Protective treatment	TC
Ambient Air Temperature for Storage	-31...158 °F (-35...70 °C)
Ambient Air Temperature for Operation	-22...122 °F (-30...50 °C)
Electrical shock protection class	Class II conforming to IEC 61140
IP degree of protection	IP53

Ordering and shipping details

Category	US100XV22617
----------	--------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	00XV
GTIN	3389119045346
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	7.68 in (19.500 cm)
Package 1 Width	5.51 in (14.000 cm)
Package 1 Length	5.51 in (14.000 cm)
Package weight(Lbs)	2.275 lb(US) (1.032 kg)
Unit Type of Package 2	S04
Number of Units in Package 2	8
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	15.75 in (40.000 cm)
Package 2 Length	23.62 in (60.000 cm)
Package 2 Weight	21.380 lb(US) (9.698 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	32
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	109.773 lb(US) (49.792 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO₂ eq, Total Life cycle) **11**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **Yes**

[EU RoHS Directive](#) **Pro-active compliance (Product out of EU RoHS legal scope)**

SCIP Number **Fe0ee3ab-dd49-4abe-bd8e-c49754e2c442**

California proposition 65 **WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)**

Use Again

Repack and remanufacture



Circularity Profile [End of Life Information](#)

Take-back **No**

Dimensions Drawings

Siren

Dimensions



Technical Illustration

Dimensions




Image of product / Alternate images

Alternative





