

Product data sheet

Specifications



additionnal EMC filter S6 M2 - 1-phase supply - 16 A

VW3A31403

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Altivar
Product or Component Type	EMC input filter
Range Compatibility	Lexium 05 Altivar 312 Altivar 31C Lexium 23 Plus Altivar 312 Solar Altivar Machine ATV320
Product compatibility	Servo drive LXM230.75 kW Servo drive LXM231 kW Servo drive LXM231.5 kW ATV312HU11M2 ATV312HU15M2 ATV31CU11M2 ATV31CU15M2 LXM05AD17F1 LXM05AD17M2 LXM05BD17F1 LXM05BD17M2 LXM05CD17M2 Variable speed drive ATV320...C1.1 kW, 200...240 V single phase Variable speed drive ATV320...C1.5 kW, 200...240 V single phase Variable speed drive ATV320...W/ATV320...WS1.1 kW, 200...240 V single phase Variable speed drive ATV320...W/ATV320...WS1.5 kW, 200...240 V single phase
Product Specific Application	Radio interference input filter
Line Rated Current	16 A
Thermal losses	6.9 W ATV31CU11M2
Phase	Single phase

Complementary

maximum earth leakage current	150 mA 50 Hz
power supply voltage	200...240 V
Tolerance	10 %
Product Weight	1.709 lb(US) (0.775 kg)

Environment

IP degree of protection	IP20 IP41 (upper part)
Relative humidity	0...93 % IEC 68-2-3
Ambient air temperature for operation	14...122 °F (-10...50 °C)
Ambient Air Temperature for Storage	-13...158 °F (-25...70 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Operating altitude	<= 3280.84 ft (1000 m) without current derating 3280.84...9842.52 ft (1000...3000 m) with current derating 1 % per 100 m
Vibration resistance	1 gn (f= 13...150 Hz) conforming to IEC 60068-2-6 1.5 mm peak to peak (f= 3...13 Hz) conforming to IEC 60068-2-6
Shock resistance	15 gn 11 ms IEC 60068-2-27
Standards	IEC 61800-3

Ordering and shipping details

Category	US1CP4B22154
Discount Schedule	CP4B
GTIN	3389110689075
Returnability	Yes
Country of origin	TH

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.97 in (5.0 cm)
Package 1 Width	7.32 in (18.6 cm)
Package 1 Length	9.53 in (24.2 cm)
Package weight(Lbs)	22.3 oz (632.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	7
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	11.118 lb(US) (5.043 kg)

Contractual warranty

Warranty	18 months
-----------------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again


Repack and remanufacture

Take-back	No
-----------	----

Dimensions Drawings

Additional EMC Input Filters

Dimensions



Dimensions in mm

a	b	c	G	H	Ø
107	195	35	85	180	4.5


Dimensions in in.

a	b	c	G	H	Ø
4.12	7.68	1.38	3.35	7.09	0.18


Mounting and Clearance

Additional EMC Input Filter


Mounting the Filter under the Drive



Mounting the Filter next to the Drive



Connections and Schema

Recommended Schema

(1) Filter

(2) Drive