

Product data sheet

Specifications



miniature plug in relay, Harmony Electromechanical Relays, 6A, 4CO, with LED, 24V AC

RXM4AB3B7

Product availability: Stock - Normally stocked in distribution facility

Main

| | |
|--|----------------------------------|
| Range of Product | Harmony Electromechanical Relays |
| Series name | RXM series |
| Product or Component Type | Plug-in relay |
| Relay Type | Miniature relay |
| Contacts type and composition | 4 C/O |
| Status LED | With |
| Control Type | Without lockable test button |
| [Uc] control circuit voltage | 24 V AC 50/60 Hz |
| [Ithe] conventional enclosed thermal current | 6 A |
| Continuous output current | 5 A |

Complementary

| | |
|---|---|
| [Uiimp] rated impulse withstand voltage | 2.5 kV 1.2/50 µs |
| [Ie] rated operational current | 3 A 28 V DC) NC IEC 3 A 250 V AC) NC IEC 6 A 28 V DC) NO IEC 6 A 250 V AC) NO IEC 6 A 277 V AC) UL 8 A 30 V DC) UL |
| Minimum switching capacity | 170 mW 10 mA, 17 V |
| Electrical durability | 100000 cycles resistive |
| Average coil consumption in VA | 1.2 60 Hz |
| Rated operational voltage limits | 19.2...26.4 V AC |
| [Ui] rated insulation voltage | 250 V IEC 300 V CSA 300 V UL |
| Average consumption | 1.2 VA 60 Hz |
| Maximum switching voltage | 250 V IEC |
| Drop-out voltage threshold | >= 0.15 Uc |
| Load current | 6 A 250 V AC 6 A 28 V DC |
| Operating time | 20 ms |
| Maximum switching capacity | 1500 VA/168 W |
| Average resistance | 180 Ohm 20 °C +/- 15 % |
| Mechanical durability | 10000000 cycles |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|--------------------------------|--|
| Safety reliability data | B10d = 100000 |
| Operating rate | <= 1200 cycles/hour under load <= 18000 cycles/hour no-load |
| Utilisation coefficient | 20 % |
| reset time | 20 ms |
| Dielectric strength | 1300 V AC between contacts with micro disconnection 2000 V AC between coil and contact with basic insulation 2000 V AC between poles with basic insulation |
| Compatibility code | RXM |
| Protection category | RT I |
| Pollution degree | 2 |
| Operating position | Any position |
| Test levels | Level A group mounting |
| Device presentation | Complete product |
| Contacts material | AgNi |
| Shape of pin | Flat (faston type) |
| Product Weight | 0.082 lb(US) (0.037 kg) |

Environment

| | |
|--|---|
| Ambient air temperature for operation | -40...131 °F (-40...55 °C) |
| IP degree of protection | IP40 conforming to IEC 60529 |
| Standards | CSA C22.2 No 14 UL 508 IEC 61810-1 |
| Product Certifications | UL Lloyd's CE CSA GOST IECEE CB Scheme |
| Ambient Air Temperature for Storage | -40...185 °F (-40...85 °C) |
| Vibration resistance | 3 gn +/- 1 mm 10...150 Hz)5 cycles in operation 5 gn +/- 1 mm 10...150 Hz)5 cycles not operating |
| Shock resistance | 10 gn in operation 30 gn not operating |

Ordering and shipping details

| | |
|--------------------------|---------------|
| Category | US10CP221127 |
| Discount Schedule | 0CP2 |
| GTIN | 3389119217217 |
| Returnability | Yes |
| Country of origin | CN |

Packing Units

| | |
|-------------------------------|--------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 0.83 in (2.100 cm) |

| | |
|------------------------------|--------------------------|
| Package 1 Width | 1.06 in (2.700 cm) |
| Package 1 Length | 1.81 in (4.600 cm) |
| Package weight(Lbs) | 1.252 oz (35.500 g) |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 1.26 in (3.200 cm) |
| Package 2 Width | 4.02 in (10.200 cm) |
| Package 2 Length | 4.96 in (12.600 cm) |
| Package 2 Weight | 13.580 oz (385.000 g) |
| Unit Type of Package 3 | S01 |
| Number of Units in Package 3 | 120 |
| Package 3 Height | 5.91 in (15.000 cm) |
| Package 3 Width | 5.91 in (15.000 cm) |
| Package 3 Length | 15.75 in (40.000 cm) |
| Package 3 Weight | 10.642 lb(US) (4.827 kg) |

Contractual warranty

Warranty 18 months



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO₂ eq, Total Life cycle) **19**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **Yes**

[EU RoHS Directive](#) **Pro-active compliance (Product out of EU RoHS legal scope)**

California proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)

Use Again


Repack and remanufacture

Circularity Profile [End of Life Information](#)


Take-back **No**

Dimensions Drawings


Dimensions

mm
in.

Pin Side View

mm
in.

Connections and Schema


Wiring Diagram

Symbols shown in blue correspond to Nema marking.

Performance Curves


Electrical Durability of Contacts

Durability (inductive load) = durability (resistive load) x reduction coefficient.
Resistive AC load




X Switching capacity (kVA)
Y Durability (Number of operating cycles)
A RXM2AB...
B RXM3AB...
C RXM4AB...
D RXM4GB...

Reduction coefficient for inductive AC load (depending on power factor $\cos \phi$)




Y Reduction coefficient (A)
Maximum switching capacity on resistive DC load



X Voltage DC
Y Current DC
A RXM2AB...
B RXM3AB...
C RXM4AB...
D RXM4GB...

Note : These are typical curves, actual durability depends on load, environment, duty cycle, etc.
For inductive load, to increase relay life cycles, please add a proper load protection circuit (eg: RC protection/Varistor/ free Wheeling diode -DC load only-).
For low level loads (below 10mA), we recommend to use RXM*GB series with bifurcated contacts relays instead.

AC Coil Voltage and Operating Temperature under continuous duty




X : Operating temperature (°C)

Y : AC coil voltage (UC)

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony RXMAB Relay

RXM*AB sockets:

- Mixed or separate contact arrangement
- Push-in, screw clamp or screw connector terminal



Plastic or metal maintaining clamp to protect against vibration

Push button (Blue for DC, Red for AC) and lockable test button for contact testing

Mechanical indicator for relay contact status

"Power On" LED for relay status

RXM*AB relays:

- 2CO-12A, 3CO-10A, 4CO-6A
- 12-220VDC, 24-240VAC

Image of product / Alternate images

Alternative

