

# Product data sheet

## Characteristics

# ACCU301

## InRow 30kW Condensing Unit, 480V, Single feed



### Main

Main Input Voltage	AC 3 phase
Provided Equipment	Installation guide Integrated network management Network Management Card User Manual

### General

Compressor Type	Scroll
Air Discharge Patterns	Upflow
Intake Air	Top Return
Piping Material	Copper

### Physical

Height	61.18 in (155.4 cm)
Width	39.41 in (100.1 cm)
Depth	39.41 in (100.1 cm)
Net Weight	588.59 lb(US) (266.98 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
USB compatible	No

### Input

Number of Power Feeds	1
Input Frequency	50/60 Hz

### Conformance

Product Certifications	CUL Listed UL Listed
------------------------	-------------------------

### Ordering and shipping details

GTIN	731304410225
Nbr. of units in pkg.	1
Package weight(Lbs)	654.77 lb(US) (297 kg)

### Packing Units

Unit Type of Package 1	BOX
Package 1 Height	44.72 in (113.6 cm)
Package 1 width	42.72 in (108.5 cm)
Package 1 Length	68.70 in (174.5 cm)

## Offer Sustainability

---

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

---

## Contractual warranty

---

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

---