


Product data sheet

Characteristics

ACRC600P

InRow RC, 600mm, Chilled Water 200-240V
50/60Hz, w/ humidifier



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

Main

Main Input Voltage	3 phase 3 phase 3 phase 3 phase
Number of rack unit	42U
Number of cables	2
Provided Equipment	Installation guide Operations and maintenance manual

General

Humidification Value	6.6 lb/hr (2.99 kg/hr)
Air Discharge Patterns	Horizontal
Intake Air	Rear Return
Air flow	6000 ft³/min (2831.68 l/s)
Minimum Water Inlet Temperature	45 °F (7 °C)
Condensate Pump Capacity	8.45 Gal/hr(US) (0.03 m3/h)

Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	23.62 in (60 cm)
Depth	42.13 in (107 cm)
Net Weight	777.66 lb(US) (352.74 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input power	14000 W
Input Frequency	50/60 Hz
Number of input connectors	1 Hard Wire 4-wire (3PH + G)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Conformance

Product Certifications	CUL Listed Industry Canada UL Listed
Standards	FCC Part 15 class A

Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity

Ordering and shipping details

GTIN	731304330370
Package weight(Lbs)	1021.14 lb(US) (463.18 kg)

Packing Units

Package 1 Height	85.28 in (216.6 cm)
Package 1 width	33.46 in (85 cm)
Package 1 Length	44.76 in (113.7 cm)
Number of Units in Package 3	1

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty	1 year (parts only), 1 year on-site repair or replace with factory authorized Start-Up
----------	--