

Product data sheet

Characteristics

AR3307X617

APC NetShelter SX, Server Rack Enclosure, 48U, without Sides and Doors, Black, 2258H x 600W x 1200D mm



Overview

Presentation

Deep and Tall Universal IT Enclosure for low to medium density server and networking applications that either require additional equipment clearance space or more open space for ease of access in the rear of the enclosure. Tall to provide 48U spaces for environments that can take advantage of higher spaces and provide more mounting u-spaces at each enclosure footprint. Compact width to optimize data center space.

Lead time

Usually in Stock

Main

Number of rack unit	48U
Provided equipment	Baying hardware Key(S) Leveling feet Mounting Hardware Pre-installed casters

Physical

Color	Black
Height	88.90 in (225.8 cm)
Width	23.62 in (60 cm)
Depth	47.24 in (120 cm)
Net Weight	329.70 lb(US) (149.55 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	41.73 in (105.99 cm)
Minimum Mounting Depth	7.52 in (19.1 cm)
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge post 18 gauge roof
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3000 lb(US) (1360.78 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

GTIN	731304293804
Package weight(Lbs)	364.76 lb(US) (165.45 kg)

Packing Units

Package 1 Height	93.90 in (238.5 cm)
Package 1 width	29.37 in (74.6 cm)
Package 1 Length	52.52 in (133.4 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------