

Product data sheet

Specifications



Editable voice alarms, Harmony XVS, black, mounting 96mm DIN rail, NPN, 100...230V AC

XVSV9MBN

Main

Range of product	Harmony XVS
Product or component type	Editable electronic alarm
Beacon or indicator bank unit type	Sound unit
Device short name	XVSV

Complementary

Colour	Dark grey
Input type	Bit: 6 channel input Binary: 63 channel input
Assembly style	Ready assembled
Material	PC (polycarbonate): body PC (polycarbonate): back cover TPE (thermoplastic elastomer): front panel NBR (nitrile butadiene rubber)
Marking	CE
Overvoltage category	Class II conforming to IEC 61140
Mounting support	96 mm DIN rail
[Us] rated supply voltage	100...230 V AC
[Ue] rated operational voltage	90...264 V AC
[Ui] rated insulation voltage	250 V
Inrush current	30 A
Associated fuse rating	1 A
[Uiimp] rated impulse withstand voltage	2.5 kV conforming to IEC 60947-1
Power consumption in W	10 W
Current consumption	100 mA at 100 V AC
Clamping connection capacity	<= 1 x 1.5 mm ²
Device application	Subway Packaging Printing
Mounting diameter	105 mm
Width	105 mm
Height	105 mm
Depth	50.1 mm
Product weight	0.287 kg

Environment

Discrete output type	NPN
Signalling type	Adjustable vocal sound
Standards	IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	-20...60 °C
Ambient air temperature for operation	0...50 °C
Pollution degree	2
Relative humidity	35...85 % without condensation
Vibration resistance	7 gn
IP degree of protection	Panel mounted: IP65 conforming to IEC 60529 Wall mounted: IP20
Noise level	0...97 dB (stop or suppress) at 1 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.600 cm
Package 1 Width	13.000 cm
Package 1 Length	17.400 cm
Package 1 Weight	591.500 g



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint

78

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

SCIP Number

Fe0ee3ab-dd49-4abe-bd8e-c49754e2c442

California proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again


Repack and remanufacture

Take-back

No


Dimensions Drawings

Dimensions




(t) : Waterproof rubber (1.6 mm / 0.06 in.)

Mounting and Clearance

Panel Cut Dimensions


(1) Installation panel

A	B	C
92 +0.6/0 mm (3.62 +0.0236/0 in.)	92 +0.6/0 mm (3.62 +0.0236/0 in.)	1...4 mm (0.04...0.15 in.)

Wall Mount Dimensions

(1) Installation panel


Connections and Schema

Wiring Diagram

- (1) Green
- (2) Yellow
- (3) Brown
- (4) Blue
- (5) Purple
- (6) Gray
- (7) White
- (8) Black
- (9) Red
- (10) Fuse (Rated current: 1 A)

Technical Illustration

Dimensions



Technical Illustration

Wiring diagram




Image of product / Alternate images

Alternative







Image of product in real life situation

