

# Product data sheet

Specifications



Triple headed push button head,  
Harmony XB4, metal, 22mm, 1  
white flush UP ARROW + 1 red  
projecting STOP + 1 black flush  
DOWN ARROW

ZB4BA71124

## Main

|                               |                                                    |
|-------------------------------|----------------------------------------------------|
| Range of product              | Harmony XB4                                        |
| Product or component type     | Head for triple-headed push-button                 |
| Device short name             | ZB4                                                |
| Bezel material                | Chromium plated metal                              |
| Mounting diameter             | 22 mm                                              |
| Sale per indivisible quantity | 1                                                  |
| Head type                     | Standard                                           |
| Shape of signaling unit head  | Rectangular                                        |
| Type of operator              | spring return                                      |
| Operator profile              | 2 flush - 1 central projecting STOP push-buttons   |
| Operators description         | White "up arrow" - black "down arrow" - red "STOP" |

## Complementary

|                                    |                                                                                                                                                                                              |
|------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product weight                     | 0.056 kg                                                                                                                                                                                     |
| Resistance to high pressure washer | 7000000 Pa at 55 °C, distance : 0.1 m                                                                                                                                                        |
| Colour of marking                  | White marking when green, red or black caps<br>Black marking when white caps                                                                                                                 |
| Operator profile                   | Red projecting, STOP (white)<br>White flush, up arrow (black)<br>Black flush, down arrow (white)                                                                                             |
| Mechanical durability              | 1000000 cycles                                                                                                                                                                               |
| Electrical composition code        | C1 for <9 contacts using single blocks in front mounting<br>C2 for <9 contacts using single and double blocks in front mounting<br>C11 for <3 contacts using single blocks in front mounting |
| Device presentation                | Basic element                                                                                                                                                                                |

## Environment

|                                       |                                 |
|---------------------------------------|---------------------------------|
| Ambient air temperature for storage   | -40...70 °C                     |
| Ambient air temperature for operation | -25...70 °C                     |
| Electrical shock protection class     | Class I conforming to IEC 60536 |
| IP degree of protection               | IP69 conforming to IEC 60529    |
| NEMA degree of protection             | NEMA 13<br>NEMA 4X              |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                |                                                                                                                                                                                |
|--------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>IK degree of protection</b> | IK06 conforming to IEC 50102                                                                                                                                                   |
| <b>Standards</b>               | IEC 60947-5-5<br>IEC 60947-5-4<br>UL 508<br>IEC 60947-1<br>IEC 60947-5-1<br>CSA C22.2 No 14<br>JIS C8201-5-1<br>JIS C8201-1                                                    |
| <b>Product certifications</b>  | CSA<br>LROS (Lloyds register of shipping)<br>BV<br>UL listed<br>DNV                                                                                                            |
| <b>Vibration resistance</b>    | 5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6                                                                                                                               |
| <b>Shock resistance</b>        | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27<br>50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |

## Packing Units

|                                     |           |
|-------------------------------------|-----------|
| <b>Unit Type of Package 1</b>       | PCE       |
| <b>Number of Units in Package 1</b> | 1         |
| <b>Package 1 Height</b>             | 3.600 cm  |
| <b>Package 1 Width</b>              | 4.600 cm  |
| <b>Package 1 Length</b>             | 5.200 cm  |
| <b>Package 1 Weight</b>             | 56.000 g  |
| <b>Unit Type of Package 2</b>       | S03       |
| <b>Number of Units in Package 2</b> | 200       |
| <b>Package 2 Height</b>             | 30.000 cm |
| <b>Package 2 Width</b>              | 30.000 cm |
| <b>Package 2 Length</b>             | 40.000 cm |
| <b>Package 2 Weight</b>             | 11.869 kg |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| <b>Warranty</b> | 18 months |
|-----------------|-----------|

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

| Environmental footprint          |                                               |
|----------------------------------|-----------------------------------------------|
| Total lifecycle Carbon footprint | 1                                             |
| Environmental Disclosure         | <a href="#">Product Environmental Profile</a> |

Use Better

| Materials and Substances               |                                                                                                                                                                                                                                                                                       |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Packaging made with recycled cardboard | Yes                                                                                                                                                                                                                                                                                   |
| Packaging without single use plastic   | Yes                                                                                                                                                                                                                                                                                   |
| <a href="#">EU RoHS Directive</a>      | Pro-active compliance (Product out of EU RoHS legal scope)                                                                                                                                                                                                                            |
| California proposition 65              | WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

Use Again


| Repack and remanufacture        |                                         |
|---------------------------------|-----------------------------------------|
| End of life manual availability | <a href="#">End of Life Information</a> |
| Take-back                       | No                                      |

Dimensions Drawings


Dimensions

---

Without Boot





With Boot ZBA709




Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

| Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board                                                                                                                                                                                                                                       | Connection by Faston Connectors                                                    |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|
|                                                                                                                                                                                                                                            |  |
| <p>(1) Diameter on finished panel or support</p> <p>(2) 40 mm min. / 1.57 in. min.</p> <p>(3) 30 mm min. / 1.18 in. min.</p> <p>(4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm <math>^{+0.4}_0</math> / 0.88 in. <math>^{+0.016}_0</math>)</p> <p>(5) 45 mm min. / 1.78 in. min.</p> <p>(6) 32 mm min. / 1.26 in. min.</p> |                                                                                    |

Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection


Panel Cut-outs (Viewed from Installer's Side)




A: 30 mm min. / 1.18 in. min.  
B: 40 mm min. / 1.57 in. min.

Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)

Dimensions in mm



A: 30 mm min.  
B: 40 mm min.  
Dimensions in in.



A: 1.18 in. min.  
B: 1.57 in. min.


General Tolerances of the Panel and Printed Circuit Board

The cumulative tolerance must not exceed 0.3 mm / 0.012 in:  $T1 + T2 = 0.3 \text{ mm max.}$

Installation Precautions

- Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm  $\pm$  0.1 / 0.88 in.  $\pm$  0.004
- Orientation of body/fixing collar ZB4 BZ009:  $\pm 2^\circ 30'$  (excluding cut-outs marked **a** and **b**).
- Tightening torque of screws ZBZ 006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB4 BZ079 fixing collar/pillar and its fixing screws:
  - every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
  - with each selector switch head (ZB4 BD\*, ZB4 BJ\*, ZB4 BG\*).

The fixing centers marked **a** and **b** are diagonally opposed and must align with those marked **4** and **5**.



(1) Panel

(2) Printed circuit board

#### Mounting of Adapter (Socket) ZBZ 01•

- 1 2 elongated holes for ZBZ 006 screw access
- 2 1 hole  $\varnothing 2.4 \text{ mm} \pm 0.05 / 0.09 \text{ in.} \pm 0.002$  for centring adapter ZBZ 01•
- 3  $8 \times \varnothing 1.2 \text{ mm} / 0.05 \text{ in.}$  holes
- 4 1 hole  $\varnothing 2.9 \text{ mm} \pm 0.05 / 0.11 \text{ in.} \pm 0.002$ , for aligning the printed circuit board (with cut-out marked **a**)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked **b**)
- 6 4 holes  $\varnothing 2.4 \text{ mm} / 0.09 \text{ in.}$  for clipping in adapter ZBZ 01•

Dimensions An + 18.1 relate to the  $\varnothing 2.4 \text{ mm} \pm 0.05 / 0.09 \text{ in.} \pm 0.002$  holes for centring adapter ZBZ 01•.



Technical Description

Electrical Composition Corresponding to Code C1

---




Electrical Composition Corresponding to Code C2

---



Electrical Composition Corresponding to Codes C9, C11, SF1 and SR1



Legend

---

Single contact



Double contact



Light block



Possible location



## Technical Illustration

## Dimensions




Image of product / Alternate images

Alternative

---

