

Product data sheet

Characteristics

AP5808

17" Rack LCD Console with Integrated 8 Port Analog KVM Switch



Overview

Presentation	The Rack LCD Console with Integrated KVM Switch combines the functionality of Rack LCD Console and Analog KVM switches in one convenient package optimizing U space in the rack environment, eliminating cable clutter, and offering a value of two products functionality in one package. Keyboard is a US English keyboard layout.
Lead time	Usually in Stock

Main

Main Input Voltage	120 V 240 V
Input Connection Type	IEC 60320 C14
Number of rack unit	1U
Cable length	6 ft (1.83 m)
Number of cables	1
Provided equipment	USB KVM cable Single user rack mount kit PS2 KVM cable NEMA 5-15 power cord Installation guide Firmware upgrade cable Documentation CD C13-C14 power cord

Physical

Color	Black
Height	1.69 in (4.3 cm)
Width	19.02 in (48.3 cm)
Depth	27.99 in (71.1 cm)
Net Weight	30.36 lb(US) (13.77 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted
Maximum Mounting Depth	41.33 in (104.98 cm)
Minimum Mounting Depth	26.77 in (68 cm)

Input

Input Frequency	50/60 Hz
-----------------	----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Conformance

Product Certifications	CUL Listed C-tick CE Industry Canada KCC UL Listed VDE TAA compliance
Standards	EN 60950 FCC Part 15 class A IEC 60950

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
---------------------------------------	-------------------------

Supported Hardware

Display colour	16 colours
Display size	337.9 (H) x 270.3 (V) 17 inch
Trackball Type	PS/2 Touchpad USB mouse
Display Type	LCD display

Ordering and shipping details

GTIN	731304278801
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.12 in (13 cm)
Package 1 Width	32.68 in (83 cm)
Package 1 Length	26.18 in (66.5 cm)
Package 1 Weight	43.78 lb(US) (19.86 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------