

Product data sheet

Characteristics

PD3P400AT5B

3-Pole Circuit Breaker, 400A, T5 Type for Symmetra PX250/500kW



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

Main

Main Input Voltage	3 phase 3 phase
Main Output Voltage	480 V 3 phase 400 V 3 phase
Output connector type	Hard Wire 3-wire (3P) 1
Provided Equipment	Installation guide

Physical

Height	17.01 in (43.2 cm)
Width	22.01 in (55.9 cm)
Depth	21.50 in (54.6 cm)
Net Weight	15.04 lb(US) (6.82 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Max line current	400 A
Input Frequency	50/60 Hz

Output

Maximum Total Current Draw per Phase	400 A
--------------------------------------	-------

Conformance

Product Certifications	CE UL Listed
------------------------	-----------------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)

Ordering and shipping details

GTIN	731304267232
Package weight(Lbs)	17.20 lb(US) (7.8 kg)

Packing Units

Package 1 Height	17.01 in (43.2 cm)
Package 1 width	22.01 in (55.9 cm)
Package 1 Length	21.50 in (54.6 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------