

# Product data sheet

Specifications



**Die cast empty control station,  
Harmony XAP, zinc alloy, grey, 3 cut  
outs, 22mm, 130x80x51.5mm**

XAPG29703

**Product availability: Stock - Normally stocked in distribution  
facility**

## Main

|                               |  |
|-------------------------------|--|
| Range of Product              | Harmony XAP                                  |
| Product or Component Type     | Die-cast empty control station               |
| Device short name             | XAPG   |
| Product destination           | For Ø 22 mm control and signalling units     |
| Number of cut-out             | 3 cut-outs                                   |
| Colour of base of enclosure   | Grey RAL 7032)                               |
| Colour of cover               | Grey RAL 7032)                               |
| Control station type          | Metal  |
| Material                      | Die cast zinc                                |
| Sale per indivisible quantity | 1  |
| IP degree of protection       | IP65 IEC 60529<br>IP657 IEC 60529            |
| Resistance to chemical agents | Special treatment can be obtained on request |

## Complementary

|                           |                                |
|---------------------------|--------------------------------|
| Number of vertical rows   | 1                              |
| Number of horizontal rows | 3                              |
| Cut-out dimensions        | Ø 22 mm                        |
| Cable entry               | cable gland<br>1 x cable gland |
| Thread type               | 3/4 NPT                        |
| CAD overall width         | 3.1 in (80 mm)                 |
| CAD overall height        | 5.1 in (130 mm)                |
| CAD overall depth         | 2.03 in (51.5 mm)              |
| Product Weight            | 1.334 lb(US) (0.605 kg)        |
| Compatibility code        | XAPG                           |

## Environment

|                                       |  |
|---------------------------------------|--|
| Protective treatment                  | TH   |
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C)   |
| Ambient Air Temperature for Operation | -13...158 °F (-25...70 °C)   |
| Electrical shock protection class     | Class I conforming to IEC 60536<br>Class I conforming to NF C 20-030 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US10CS222475  |
| Discount Schedule | OCS2          |
| GTIN              | 3389118381810 |
| Returnability     | Yes           |
| Country of origin | MA            |

## Packing Units

|                              |                          |
|------------------------------|--------------------------|
| Unit Type of Package 1       | PCE                      |
| Nbr. of units in pkg.        | 1                        |
| Package 1 Height             | 3.74 in (9.500 cm)       |
| Package 1 Width              | 3.50 in (8.900 cm)       |
| Package 1 Length             | 6.10 in (15.500 cm)      |
| Package weight(Lbs)          | 24.233 oz (687.000 g)    |
| Unit Type of Package 2       | S03                      |
| Number of Units in Package 2 | 12                       |
| Package 2 Height             | 11.81 in (30.000 cm)     |
| Package 2 Width              | 11.81 in (30.000 cm)     |
| Package 2 Length             | 15.75 in (40.000 cm)     |
| Package 2 Weight             | 19.363 lb(US) (8.783 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Carbon footprint (kg CO<sub>2</sub> eq, Total Life cycle) **5**

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **Yes**

[EU RoHS Directive](#) **Pro-active compliance (Product out of EU RoHS legal scope)**

California proposition 65 **WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)**

## Use Again

### Repack and remanufacture


Circularity Profile **No need of specific recycling operations**

Take-back **No**

## Offer Marketing Illustration

## Product benefits / Features

### Technical Benefits XAP



## Offer Marketing Illustration

## Product benefits / Features



Image of product / Alternate images

Alternative

---





