

Product data sheet

Specifications



Add-on contact block, TeSys Deca Frame 2/3, 1NO(fault)+1NC, side, for GV2/GV3(except GV3ME)

GVAD1001

Main

Range	TeSys TeSys Deca
Device short name	GVAD
Product or component type	Auxiliary contact block
Product compatibility	GV2P GV2LE GV3L GV2ME GV2RT GV3P GV2L
Mounting location	Left side
Auxiliary contacts operation	Fault signal 1 NO
Pole contact composition	1 NO + 1 NC

Complementary

[Ui] rated insulation voltage	690 V conforming to IEC 60947-1 300 V conforming to UL 508 300 V conforming to CSA C22.2 No 14
[Ue] rated operational voltage	48...690 V AC 24...240 V DC
[Ith] conventional free air thermal current	6 A 2.5 A for fault signalling
Mechanical durability	100000 cycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Protection type	GB2CB... circuit breaker GG fuse 10 A
Rated operational power in VA	300 VA at 48 V AC-15 - electrical durability: 100000 cycles 414 VA at 690 V AC-15 - electrical durability: 100000 cycles 500 VA at 110...127 V AC-15 - electrical durability: 100000 cycles 500 VA at 500 V AC-15 - electrical durability: 100000 cycles 650 VA at 440 V AC-15 - electrical durability: 100000 cycles 720 VA at 230...240 V AC-15 - electrical durability: 100000 cycles 850 VA at 380...415 V AC-15 - electrical durability: 100000 cycles 36 VA at 24 V AC-14 - electrical durability: 1000 cycles 48 VA at 48 V AC-14 - electrical durability: 1000 cycles 72 VA at 110...127 V AC-14 - electrical durability: 1000 cycles

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Rated operational power in W	120 W at 240 V DC-13 - electrical durability: 100000 cycles 140 W at 110 V DC-13 - electrical durability: 100000 cycles 140 W at 24 V DC-13 - electrical durability: 100000 cycles 180 W at 60 V DC-13 - electrical durability: 100000 cycles 240 W at 48 V DC-13 - electrical durability: 100000 cycles 15 W at 48 V DC-13 - electrical durability: 1000 cycles 24 W at 24 V DC-13 - electrical durability: 1000 cycles 9 W at 60 V DC-13 - electrical durability: 1000 cycles
Tightening torque	1.4 N.m - on screw clamp terminals
Height	89 mm
Width	9.3 mm
Depth	66 mm
Product weight	0.055 kg
Colour	Dark grey

Environment

Environmental characteristic	Normal environment
Product certifications	UKCA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	6.500 cm
Package 1 Length	9.000 cm
Package 1 Weight	46.500 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.500 cm
Package 2 Width	9.500 cm
Package 2 Length	15.000 cm
Package 2 Weight	516.000 g
Unit Type of Package 3	S02
Number of Units in Package 3	60
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	3.347 kg

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Total lifecycle Carbon footprint	1
Environmental Disclosure	Product Environmental Profile

Use Better


Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Connections and Schema

GVAD1001



Technical Illustration

Assembly's dimensions

