

# Product data sheet

Specifications



Discrete I/O expansion block,  
Modicon TM7, IP67, 8 DO, 24 V DC,  
2 A, M8 connector

TM7BDO8TAB

## Main

Range of product	Modicon TM7
Product or component type	Discrete I/O expansion block
Range compatibility	Modicon LMC058 Modicon M258
Enclosure material	Plastic
Bus type	TM7 bus
[Ue] rated operational voltage	24 V DC
Input/output number	8
input/output number of block	8 O

## Complementary

Discrete output number	8 at <= 2 A with transistor protection
Discrete output voltage	24 V
Discrete output voltage type	DC
Sensor power supply	24 V, 500 mA for all channels with overload, short-circuit and reverse polarity protection
Electrical connection	1 male connector M12 - B coding - 4 ways for bus IN 1 female connector M12 - B coding - 4 ways for bus OUT 1 male connector M8 - 4 ways for power IN 1 female connector M8 - 4 ways for power OUT 1 female connector M8 - 3 ways for actuator
Local signalling	2 LEDs for bus diagnostic 2 LEDs for sensor power supply diagnostics
Operating position	Any position
fixing mode	By 2 screws
Product weight	0.185 kg

## Environment

Standards	IEC 61131-2
Product certifications	GOST-R C-Tick ATEX II 3g EEx nA II T5 cURus
Marking	CE
Ambient air temperature for operation	-10...60 °C
Ambient air temperature for storage	-25...85 °C

<b>Relative humidity</b>	5...95 % without condensation or dripping water
<b>Pollution degree</b>	2 conforming to IEC 60664
<b>IP degree of protection</b>	IP67 conforming to IEC 61131-2
<b>Operating altitude</b>	0...2000 m
<b>Storage altitude</b>	0...3000 m
<b>Vibration resistance</b>	7.5 mm constant amplitude (f= 2...8 Hz) conforming to IEC 60721-3-5 Class 5M3 2 gn constant acceleration (f= 8...200 Hz) conforming to IEC 60721-3-5 Class 5M3 4 gn constant acceleration (f= 200...500 Hz) conforming to IEC 60721-3-5 Class 5M3
<b>Shock resistance</b>	30 gn for 11 ms conforming to IEC 60721-3-5 Class 5M3
<b>Electromagnetic compatibility</b>	Electrostatic discharge immunity test, 4 kV on contact conforming to IEC 61000-4-2 Electrostatic discharge immunity test, 8 kV in air conforming to IEC 61000-4-2 Susceptibility to electromagnetic fields, 1 V/m 2...2.7 GHz conforming to IEC 61000-4-3 Susceptibility to electromagnetic fields, 10 V/m 80...2000 MHz conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test, 2 kV power supply conforming to IEC 61000-4-4 Electrical fast transient/burst immunity test, 1 kV input/output conforming to IEC 61000-4-4 Electrical fast transient/burst immunity test, 1 kV shielded cable conforming to IEC 61000-4-4 1.2/50 $\mu$ s shock waves immunity test, 0.5 kV power supply (common mode) conforming to IEC 61000-4-5 1.2/50 $\mu$ s shock waves immunity test, 1 kV power supply (differential mode) conforming to IEC 61000-4-5 1.2/50 $\mu$ s shock waves immunity test, 0.5 kV unshielded links (common mode) conforming to IEC 61000-4-5 1.2/50 $\mu$ s shock waves immunity test, 1 kV unshielded links (differential mode) conforming to IEC 61000-4-5 1.2/50 $\mu$ s shock waves immunity test, 0.5 kV shielded links (common mode) conforming to IEC 61000-4-5 1.2/50 $\mu$ s shock waves immunity test, 1 kV shielded links (differential mode) conforming to IEC 61000-4-5 Conducted RF disturbances conforming to IEC 61000-4-6 Conducted and radiated emissions conforming to CISPR 11

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	5.000 cm
<b>Package 1 Width</b>	5.900 cm
<b>Package 1 Length</b>	10.500 cm
<b>Package 1 Weight</b>	203.000 g
<b>Unit Type of Package 2</b>	S02
<b>Number of Units in Package 2</b>	24
<b>Package 2 Height</b>	15.000 cm
<b>Package 2 Width</b>	30.000 cm
<b>Package 2 Length</b>	40.000 cm
<b>Package 2 Weight</b>	5.222 kg

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard No

Packaging without single use plastic Yes

[EU RoHS Directive](#) Pro-active compliance (Product out of EU RoHS legal scope)

REACH Regulation [REACH Declaration](#)

California proposition 65 WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)

PVC free Yes

## Use Again

### Repack and remanufacture

End of life manual availability [End of Life Information](#)


Take-back No

WEEE Label  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Presentation

Digital Output Block

## Description



- (A) TM7 bus IN connector
- (B) TM7 bus OUT connector
- (C) 24 Vdc power IN connector
- (D) 24 Vdc power OUT connector
- (1) Output connectors
- (2) Status LEDs


## Connector and Channel Assignments

Output connectors	Channel type	Channels
1	Output	Q0
2	Output	Q1
3	Output	Q2
4	Output	Q3
5	Output	Q4
6	Output	Q5
7	Output	Q6
8	Output	Q7


## Dimensions Drawings

TM7 Block, Size 1

## Dimensions




## Mounting and Clearance


Spacing Requirements

1 Straight cable

2 Elbowed cable

**Installation Guidelines****TM7 Block on an Aluminium Frame**


NOTE: Maximum torque to fasten the required M4 screws is 0.6 N.m (5.3 lbf-in).

**TM7 Block on a DIN Rail**


NOTE: Only size 1 (smallest) blocks can be installed on DIN rail with the TM7ACMP mounting plate.

**TM7 Block Directly on the Machine**

Drilling template of the block:

mm  
in.


(1)



(2)

- (1) Size 1
- (2) Size 2


The thickness of the base plate should be taken into consideration when defining the screw length.



NOTE: Maximum torque to fasten the required M4 screws is 0.6 N.m (5.3 lbf-in).

## Connections and Schema


Wiring Diagram**Pin Assignments for Output Connectors**

Connection	Pin	M8 Output
	1	24 Vdc actuator supply
	3	0 Vdc
	4	DO: output signal

### Wiring the Power Supply

When you provide power to a TM7 I/O block using the 24 VDC Power OUT connector of the preceding I/O block, both blocks occupy the same 24 Vdc I/O power segment. However, if you connect an external isolated power supply to the 24 Vdc Power IN connector of a TM7 I/O block, you establish a new 24 Vdc I/O power segment beginning with that I/O block.


I/O block wired with one external 24 Vdc power supply:



(3) External fuse, Type T slow-blow, 8 A max., 250 V

PS2 External isolated I/O power supply, 24 Vdc

## Performance Curves

Switching Inductive Load Characteristics

- (1) Load resistance in  $\Omega$
- (2) Load inductance in H
- (3) Max. operating cycles / second