

Product data sheet

Specifications



**Illuminated monolithic push button,
Harmony XB6E, square yellow flush,
16mm, spring return 12VDC, 1CO**

XB6ECW5J1P

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony XB6E
Product or Component Type	Illuminated monolithic push-button
Device short name	XB6E
Bezel material	Plastic
Mounting diameter	0.6 in (16 mm)
Sale per indivisible quantity	5
Shape of signaling unit head	Square
Type of operator	spring return
Operator profile	Yellow flush
Contacts type and composition	1 C/O
Contact operation	Snap action
Connections - terminals	Insulated faston 2.8 x 0.5 mm Solder terminal <= 0.75 mm ² AWG 19 Fast connector socket
Contacts material	Gold-flashed silver
Light source	Integral LED
[Us] rated supply voltage	12 V DC polarised

Complementary

Product Weight	0.013 lb(US) (0.006 kg)
Operating position	Any position
Marking	CE
Mechanical durability	1000000 cycles
Contact resistance	50 mOhm 1/6 V
Short-circuit protection	2 A cartridge fuse gG
[Ith] conventional free air thermal current	3 A fast connector socket) 5 A
[Ie] rated operational current	1.5 A 120 V, AC-12 IEC 60947-5-1 1 A 240 V, AC-12 IEC 60947-5-1 1 A 24 V, DC-12 IEC 60947-5-1 0.7 A 24 V, DC-13 IEC 60947-5-1 0.2 A 125 V, DC-12 IEC 60947-5-1 0.15 A 125 V, DC-13 IEC 60947-5-1
Electrical durability	100000 cycles, AC, 0.7 A 220 V IEC 60947-5-1 appendix C
Signalling type	Steady

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Current Consumption	10 mA
---------------------	-------

Service life	30000 h
--------------	---------

Environment

Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
-------------------------------------	----------------------------

Ambient Air Temperature for Operation	14...131 °F (-10...55 °C)
---------------------------------------	---------------------------

IP degree of protection	IP65 IEC 60529
-------------------------	----------------

Standards	JIS C 4520 UL 508 IEC 60947-5-1 IEC 60947-1 JIS C 852 CSA C22.2 No 14
-----------	--

Product Certifications	cURus CCC
------------------------	--------------

Vibration resistance	1 mm (f= 10...55 Hz) conforming to IEC 60068-2-6
----------------------	--

Shock resistance	10 gn 11 ms) half sine wave acceleration IEC 60068-2-27
------------------	---

Ordering and shipping details

Category	US10CS222459
Discount Schedule	0CS2
GTIN	3389110626766
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.98 in (2.500 cm)
Package 1 Width	4.72 in (12.000 cm)
Package 1 Length	2.63 in (6.670 cm)
Package weight(Lbs)	0.353 oz (10.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	0.98 in (2.500 cm)
Package 2 Width	4.72 in (12.000 cm)
Package 2 Length	7.87 in (20.000 cm)
Package 2 Weight	2.046 oz (58.000 g)
Unit Type of Package 3	S01
Number of Units in Package 3	50
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	5.91 in (15.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	29.630 oz (840.000 g)

Contractual warranty

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again


Repack and remanufacture

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Dimensions Drawings

Pushbutton

Square Head



(1) Anti-rotation plate (thickness: 0.6 mm / 0.02 in.)

(2) Seal (thickness: 0.5 mm / 0.01 in.)

e panel thickness: 0.5 mm (0.01 in.) $\leq e \leq$ 6 mm (0.24 in.)

Mounting and Clearance

Panel Cut-Out and Mounting

Circular or Square Head

