

Product data sheet

Specifications



APC NetShelter Basic Rack PDU,
1U, 30A, 120V, 10 NEMA 5-20
outlets

AP9560

Product availability: Non-Stock - Not normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

Color	Black
Product or Component Type	PDU
PDU Type	Basic
Cord length	12 ft (3.7 m)
Number of cables	1
Provided Equipment	User Manual Rack Mounting brackets

Complementary

Input Voltage	100 V 120 V
Height	1.73 in (4.4 cm)
Width	17.60 in (44.7 cm)
Output Voltage	120 V
Depth	2.24 in (5.7 cm)
Product Weight	5.5 lb(US) (2.5 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Input Plug Type	NEMA L5-30P
Mounting Mode	Rack-mounted
Rack units	1U
Mounting position	Horizontal
Line Rated Current	24 A
permissible voltage	90...132 V
Max line current	24 A
Input current limits	30 A
Load Capacity	2880 VA
Input Frequency	50/60 Hz
Outlet type and quantity	10 NEMA 5-20R

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Product Certifications	cUL Listed UL Listed
Standards	UL 60950
Ambient Air Temperature for Operation	5...113 °F (-15...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304192930
Returnability	No
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	5.98 in (15.2 cm)
Package 1 Width	6.97 in (17.7 cm)
Package 1 Length	19.13 in (48.6 cm)
Package weight(Lbs)	8.02 lb(US) (3.64 kg)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	64
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
Halogen content performance	Product contains halogen above thresholds

Energy efficiency

Optimized Energy Efficiency	Energy efficient product
-----------------------------	--------------------------

Use Again

Repack and remanufacture

Circularity Profile	End of Life Information
Take-back	No

Image of product / Alternate images

Alternative



