

# Product data sheet

Specifications



Head for key selector switch,  
Harmony XB5, plastic, black, 22mm,  
key 458A, 2 positions, stay put

ZB5AG210

Product availability: Stock - Normally stocked in distribution facility

## Main

|                               |                              |
|-------------------------------|------------------------------|
| Range of Product              | Harmony XALF<br>Harmony XB5  |
| Product or Component Type     | Head for key selector switch |
| Device short name             | ZB5                          |
| Bezel material                | Dark grey plastic            |
| Mounting diameter             | 0.9 in (22 mm)               |
| Head type                     | Standard                     |
| Sale per indivisible quantity | 1                            |
| Shape of signaling unit head  | Round                        |
| Type of operator              | stay put                     |
| Operator profile              | Black key switch             |
| Operator position information | 2 positions 90°              |
| Type of Keylock               | Key 458A                     |
| Key withdrawal position       | Left                         |

## Complementary

|                             |                                                                                                                                                                                                                                                                                                                                              |
|-----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| CAD overall width           | 1.1 in (29 mm)                                                                                                                                                                                                                                                                                                                               |
| CAD overall height          | 1.1 in (29 mm)                                                                                                                                                                                                                                                                                                                               |
| CAD overall depth           | 2.8 in (72 mm)                                                                                                                                                                                                                                                                                                                               |
| Product Weight              | 0.126 lb(US) (0.057 kg)                                                                                                                                                                                                                                                                                                                      |
| Mechanical durability       | 1000000 cycles                                                                                                                                                                                                                                                                                                                               |
| Station name                | XALD 1...5 cut-outs<br>XALK 2...5 cut-outs                                                                                                                                                                                                                                                                                                   |
| Electrical composition code | C4 6 single and double front mounting<br>C5 5 single front mounting<br>C6 5 single and double front mounting<br>C7 4 single front mounting<br>C8 4 single and double front mounting<br>C11 3 single front mounting<br>C3 6 single front mounting<br>SF1 3 single front mounting<br>SR1 3 single rear mounting<br>C15 1 single front mounting |
| Device presentation         | Basic element                                                                                                                                                                                                                                                                                                                                |

## Environment

|                      |    |
|----------------------|----|
| Protective treatment | TH |
|----------------------|----|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                       |                                                                                                                    |
|---------------------------------------|--------------------------------------------------------------------------------------------------------------------|
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C)                                                                                         |
| Ambient Air Temperature for Operation | -40...158 °F (-40...70 °C)                                                                                         |
| Overvoltage category                  | Class II conforming to IEC 60536                                                                                   |
| IP degree of protection               | IP66 IEC 60529<br>IP67<br>IP69<br>IP69K                                                                            |
| NEMA degree of protection             | NEMA 13<br>NEMA 4X                                                                                                 |
| Resistance to high pressure washer    | 1015.3 psi (7000000 Pa) 131 °F (55 °C) 0.1 m                                                                       |
| IK degree of protection               | IK06 conforming to IEC 50102                                                                                       |
| Standards                             | IEC 60947-5-4<br>IEC 60947-1<br>IEC 60947-5-1<br>CSA C22.2 No 14<br>UL 508<br>JIS C8201-5-1<br>JIS C8201-1         |
| Product Certifications                | DNV<br>CSA<br>BV<br>LROS (Lloyds register of shipping)<br>UL Listed                                                |
| Vibration resistance                  | 5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6                                                                   |
| Shock resistance                      | 30 gn 18 ms) half sine wave acceleration IEC 60068-2-27<br>50 gn 11 ms) half sine wave acceleration IEC 60068-2-27 |

## Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US10CS222467  |
| Discount Schedule | 0CS2          |
| GTIN              | 3389110135244 |
| Returnability     | Yes           |
| Country of origin | FR            |

## Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Nbr. of units in pkg.        | 1                       |
| Package 1 Height             | 1.26 in (3.200 cm)      |
| Package 1 Width              | 2.13 in (5.400 cm)      |
| Package 1 Length             | 3.23 in (8.200 cm)      |
| Package weight(Lbs)          | 2.434 oz (69.000 g)     |
| Unit Type of Package 2       | S02                     |
| Number of Units in Package 2 | 50                      |
| Package 2 Height             | 5.91 in (15.000 cm)     |
| Package 2 Width              | 11.81 in (30.000 cm)    |
| Package 2 Length             | 15.75 in (40.000 cm)    |
| Package 2 Weight             | 8.029 lb(US) (3.642 kg) |

# Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

|  Environmental footprint |                                               |
|-----------------------------------------------------------------------------------------------------------|-----------------------------------------------|
| Carbon footprint (kg CO2 eq, Total Life cycle)                                                            | 1                                             |
| Environmental Disclosure                                                                                  | <a href="#">Product Environmental Profile</a> |

Use Better

|  Materials and Substances |                                                                                                                                                                                                                                                                                             |
|------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Packaging made with recycled cardboard                                                                     | No                                                                                                                                                                                                                                                                                          |
| Packaging without single use plastic                                                                       | No                                                                                                                                                                                                                                                                                          |
| <a href="#">EU RoHS Directive</a>                                                                          | Pro-active compliance (Product out of EU RoHS legal scope)                                                                                                                                                                                                                                  |
| SCIP Number                                                                                                | F28cb399-1b6a-409d-ac7b-4169e47b25c8                                                                                                                                                                                                                                                        |
| California proposition 65                                                                                  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |


Use Again

|  Repack and remanufacture |                                         |
|--------------------------------------------------------------------------------------------------------------|-----------------------------------------|
| Circularity Profile                                                                                          | <a href="#">End of Life Information</a> |
| Take-back                                                                                                    | No                                      |

Dimensions Drawings

Dimensions


---



Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support  
(2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.  
(3) Ø22.5 mm recommended ( $\text{Ø}22.3 \begin{smallmatrix} +0.4 \\ 0 \end{smallmatrix}$ ) / Ø0.89 in. recommended ( $\text{Ø}0.88 \text{ in.} \begin{smallmatrix} +0.016 \\ 0 \end{smallmatrix}$ )

| Connections                                   | a in mm | a in in. | b in mm | b in in. |
|-----------------------------------------------|---------|----------|---------|----------|
| By screw clamp terminals or plug-in connector | 40      | 1.57     | 30      | 1.18     |
| By Faston connectors                          | 45      | 1.77     | 32      | 1.26     |
| On printed circuit board                      | 30      | 1.18     | 30      | 1.18     |


Detail of Lug Recess



- (1) Diameter on finished panel or support  
(2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.  
(3) Ø22.5 mm recommended ( $\text{Ø}22.3 \begin{smallmatrix} +0.4 \\ 0 \end{smallmatrix}$ ) / Ø0.89 in. recommended ( $\text{Ø}0.88 \text{ in.} \begin{smallmatrix} +0.016 \\ 0 \end{smallmatrix}$ )

Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection


Panel Cut-outs (Viewed from Installer’s Side)




A: 30 mm min. / 1.18 in. min.  
B: 40 mm min. / 1.57 in. min.

Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)

Dimensions in mm



A: 30 mm min.  
B: 40 mm min.  
Dimensions in in.



A: 1.18 in. min.  
B: 1.57 in. min.


General Tolerances of the Panel and Printed Circuit Board

The cumulative tolerance must not exceed 0.3 mm / 0.012 in.: T1 + T2 = 0.3 mm max.

Installation Precautions

- Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm ± 0.1 / 0.88 in. ± 0.004
- Orientation of body/fixing collar ZB5AZ009: ± 2° 30' (excluding cut-outs marked a and b).
- Tightening torque of screws ZBZ006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB5AZ079 fixing collar/pillar and its fixing screws:
  - every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
  - with each selector switch head (ZB5AD\*, ZB5AJ\*, ZB5AG\*).

The fixing centers marked a and b are diagonally opposed and must align with those marked 4 and 5.





- (1) Head ZB5AD•
- (2) Panel
- (2) Nut
- (4) Printed circuit board

## Mounting of Adapter (Socket) ZBZ01•

- 1 2 elongated holes for ZBZ006 screw access
- 2 1 hole  $\varnothing$  2.4 mm  $\pm$  0.05 / 0.09 in.  $\pm$  0.002 for centring adapter ZBZ01•
- 3 8  $\times$   $\varnothing$  1.2 mm / 0.05 in. holes
- 4 1 hole  $\varnothing$  2.9 mm  $\pm$  0.05 / 0.11 in.  $\pm$  0.002, for aligning the printed circuit board (with cut-out marked **a**)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked **b**)
- 6 4 holes  $\varnothing$  2.4 mm / 0.09 in. for clipping in adapter ZBZ01•

Dimensions An + 18.1 relate to the  $\varnothing$  2.4 mm  $\pm$  0.05 / 0.09 in.  $\pm$  0.002 holes for centring adapter ZBZ01•.

Technical Description


Electrical Composition Corresponding to Code C4

---



Electrical Composition Corresponding to Code C5

---




Electrical Composition Corresponding to Code C6

---




Electrical Composition Corresponding to Code C7

---



Electrical Composition Corresponding to Code C8

---




Electrical Composition Corresponding to Code C3

---



Electrical Composition Corresponding to Codes C9, C11, SF1 and SR1





Legend

---

Single contact



Double contact



Light block



Possible location



Sequence of Contacts Fitted to 2-position Selector Switch Body

Position 315°



|          |          |        |        |        |        |
|----------|----------|--------|--------|--------|--------|
| Push     | Position | Top    |        |        |        |
|          |          | Bottom |        |        |        |
|          | Location |        | Left   | Centre | Right  |
|          | State    |        | 0      | 0      | 0      |
|          |          |        |        |        |        |
| Contacts | N/O      |        | open   | open   | open   |
|          | N/C      |        | closed | closed | closed |


Position 45°



|          |          |        |        |        |        |
|----------|----------|--------|--------|--------|--------|
| Push     | Position | Top    |        |        |        |
|          |          | Bottom |        |        |        |
|          | Location |        | Left   | Centre | Right  |
|          | State    |        | 1      | 1      | 1      |
|          |          |        |        |        |        |
| Contacts | N/O      |        | closed | closed | closed |
|          | N/C      |        | open   | open   | open   |

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features

---

Technical Benefits

Harmony XB5



Offer Marketing Illustration

Product benefits / Features

### Features

Harmony XB5



Quick and easy assembly and disassembly



Excellent mechanical connection with operator head



Various types of connection: screw clamp, connector, Faston connector, spring terminal, or printed circuit board



Robustness to withstand harsh environments



Large set of accessories to customize your panels



Image of product / Alternate images

Alternative

---





