

Product data sheet

Specifications



Selector switch head, Harmony
9001K, metal, without handle,
30mm, 4 positions, stay put

9001KS88

Main

Range of product	Harmony 9001K
Product or component type	Head for selector switch
Device short name	K
Type of operator	maintained
Operator profile	Without cap without knob

Complementary

Bezel material	Metal
Mounting diameter	30 mm
Operator position information	4 positions
Contacts type and composition	Without contact block
Device presentation	Basic element
Operator profile	Without handle
Type of operator	Stay put
Size	30 mm
Cam profile	8

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	CSA LR24590 class 3211 03 CE UL listed file E42259 CCN NKCR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.6 cm
Package 1 Width	5.799 cm
Package 1 Length	5.301 cm
Package 1 Weight	117.934 g



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins