

# Product data sheet

Specifications



Panel mounted timer monofunction,  
Harmony XB5, plastic, 22mm, time  
delay 3...60min, 24V DC

XB5DTB25

Product availability: Non-Stock - Not normally stocked in  
distribution facility

## Main

Range of Product Harmony XB5

Product or Component Type Timer

Sale per indivisible quantity 1

## Complementary

Bezel material Plastic

Fixing collar material Plastic

Mounting diameter 0.9 in (22 mm)

Panel Thickness 0.04...0.2 in (1...6 mm)

Shape of signaling unit head Round

Time delay range 3...60 min

Time delay type A

Repeat accuracy +/- 0.5 %

Setting accuracy of time delay +/- 10 % of full scale 77 °F (25 °C) IEC 61812-1

Temperature Drift +/- 0.05 %/°C

Voltage drift +/- 0.2 %/V

Protection Type Reverse polarity protection  
Overvoltage protection

Pollution degree 3 IEC 60664-1

Output Type Open collector PNP

Temporary permissible current 10 A 0.01 s

minimum switching current 10 mA

Voltage drop in closed state 3 V

Nominal rating 200 mA at 68 °F (20 °C) (derating 1.5 mA per °C)

Residual current in open state 0.1 mA

Power Consumption in W 1 W

Reset time 5 ms after time delay on de-energisation  
7 ms during time delay on de-energisation

Local signalling LED green, flashing timing in progress  
LED, steady no timing in progress and output relay energised

[Us] rated supply voltage 24 V DC

Supply voltage limits 16.8...31.2 V DC

Output short-circuit protection Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

|   |   |
|---|---|
| <b>Connections - terminals</b>                            | Screw terminals 1 x 4 mm <sup>2</sup> IEC 60947-1<br>Screw terminals 1 x 2.5 mm <sup>2</sup> IEC 60947-1  |
| <b>IP degree of protection</b>                            | IP65 front: conforming to IEC 60529<br>IP20 back: conforming to IEC 60529   |
| <b>Ambient Air Temperature for Operation</b>              | -4...140 °F (-20...60 °C)   |
| <b>Ambient Air Temperature for Storage</b>                | -4...176 °F (-20...80 °C)   |
| <b>Tightening torque</b>                                  | 4.4 lbf.in (0.5 N.m)  |
| <b>Dielectric strength</b>                                | 1500 V IEC 61812-1  |
| <b>[Ui] rated insulation voltage</b>                      | 50 V IEC 60947-1<br>50 V IEC 60664-1  |
| <b>[Ui<sub>imp</sub>] rated impulse withstand voltage</b> | 4 kV IEC 60947-1<br>4 kV IEC 60664-1  |
| <b>Surge withstand</b>                                    | 1 kV, level 2 IEC 61000-4-5   |
| <b>Overvoltage category</b>                               | Class 3 conforming to IEC 60536<br>Class 3 conforming to IEC 60664-1  |
| <b>Vibration resistance</b>                               | 0.15 mm (f= 10...60 Hz) conforming to IEC 60068-2-6<br>2 gn (f= 60...150 Hz) conforming to IEC 60068-2-6  |
| <b>Shock resistance</b>                                   | +/- 15 gn 11 ms 6 shocks on each axis)IEC 60068-2-27  |
| <b>Resistance to fast transients</b>                      | 2 kV level 3 IEC 61000-4-4  |
| <b>Electromagnetic compatibility</b>                      | Electrostatic discharge 6 kV level 3 conforming to IEC 61000-4-2<br>Electromagnetic emission class B conforming to IEC 55011                                    |
| <b>Resistance to electromagnetic fields</b>               | 9.1 V/m (10 V/m) 80 MHz...1 GHz level 3 IEC 61000-4-3<br>2.7 V/m (3 V/m) 1.4...2 GHz level 2 IEC 61000-4-3<br>0.9 V/m (1 V/m) 2...2.7 GHz level 1 IEC 61000-4-3 |
| <b>Immunity to radioelectric fields</b>                   | 10 V level 3 IEC 61000-4-6  |
| <b>Disturbance radiated/conducted</b>                     | Class B EN 50022  |
| <b>Standards</b>  | UL 508<br>IEC 61812-1   |
| <b>Product Certifications</b>                             | UL Listed<br>CE   |
| <b>Device presentation</b>                                | Monolithic product  |
| <b>Height</b>   | 2.4 in (62 mm)  |
| <b>Width</b>  | 1.1 in (29 mm)  |
| <b>Depth</b>  | 1.1 in (29 mm)  |
| <b>Product Weight</b>                                     | 0.060 lb(US) (0.027 kg)   |
| <b>Diameter</b>   | 1.1 in (29 mm)  |

## Ordering and shipping details

|                          |               |
|--------------------------|---------------|
| <b>Category</b>          | US10CS200028  |
| <b>Discount Schedule</b> | 0CS2          |
| <b>GTIN</b>              | 3606481205490 |
| <b>Returnability</b>     | Yes           |
| <b>Country of origin</b> | FR            |

## Packing Units

|                               |     |
|-------------------------------|-----|
| <b>Unit Type of Package 1</b> | PCE |
|-------------------------------|-----|

|                                     |                    |
|-------------------------------------|--------------------|
| <b>Nbr. of units in pkg.</b>        | 1                  |
| <b>Package 1 Height</b>             | 1.26 in (3.2 cm)   |
| <b>Package 1 Width</b>              | 1.26 in (3.2 cm)   |
| <b>Package 1 Length</b>             | 2.95 in (7.5 cm)   |
| <b>Package weight(Lbs)</b>          | 1.06 oz (30.0 g)   |
| <b>Unit Type of Package 2</b>       | S01                |
| <b>Number of Units in Package 2</b> | 24                 |
| <b>Package 2 Height</b>             | 5.91 in (15.0 cm)  |
| <b>Package 2 Width</b>              | 5.91 in (15.0 cm)  |
| <b>Package 2 Length</b>             | 15.75 in (40.0 cm) |
| <b>Package 2 Weight</b>             | 32.1 oz (911.0 g)  |



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Use Better

### Materials and Substances

|  |   |
|--|---|
| Packaging made with recycled cardboard | No  |
| Packaging without single use plastic   | No  |
| <a href="#">EU RoHS Directive</a>      | Pro-active compliance (Product out of EU RoHS legal scope)  |
| California proposition 65              | <b>WARNING:</b> This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a> |


## Use Again

### Repack and remanufacture

|           |    |
|-----------|----|
| Take-back | No |
|-----------|----|

## Dimensions Drawings

## Dimensions



(e) Clamping thickness: 1 mm to 6 mm / 0.03 in. to 0.24 in.


(1) Sealing ring

(2) Screw

## Mounting and Clearance

Panel Cut-out for Analog Timer (Finished Holes, Ready for Installation)

## Connection by Screw Clamp Terminals or Plug-in Connectors




(1) Diameter on finished panel or support

(2) Ø22 mm recommended (Ø22.3 0+0.4) / Ø0.89 in. recommended (Ø0.88 in. 0<sup>+0.016</sup>)

| Connections                                   | a in mm | a in in. | b in mm | b in in. |
|---|---------|----------|---------|----------|
| By screw clamp terminals or plug-in connector | 50      | 1.97     | 30      | 1.18     |

## Connections and Schema

Wiring Diagram

T : Timer

(1) Load

A1 - A2 : Supply (24VDC)

## Technical Description

**Function A : On Delay Timer****Description**


The timing period T begins on energisation with blinking LED indication. After timing, the output (18) closes and LED goes steady

**Function: Output**

-  De-energised
-  Energised
-  Output open
-  Output closed
- (18) Timed output
- (A1- A2) Supply

## Technical Illustration


## Dimensions



Technical Illustration

**Wiring diagram**

---



## Offer Marketing Illustration

## Product benefits / Features

## Features

### Harmony XB5



- Quick and easy assembly and disassembly**  

- Excellent mechanical connection with operator head**  

- Various types of connection: screw clamp, connector, Faston connector, spring terminal, or printed circuit board**  

- Large set of accessories to customize your panels**  

- Robustness to withstand harsh environments**  


## Offer Marketing Illustration

## Product benefits / Features

## Technical Benefits

## Harmony XB5

Conformity with IEC, UL, CSA, CCC EAC, and JIS standards, as well as CE marking and marine approvals



Operating temperature from -40°C to 70°C

Up to IP66, 67, 69, 69K, and type 4X protection ratings



Shock protection level up to IK06

High vibration resistance with shake-proof terminal screws

Secure switching of inductive or heavy DC loads directly – 100 000 operations at 10A, 24V dc

Image of product / Alternate images

Alternative

---



