

# Product data sheet

Specifications



## Regulated Power Supply, 100...240V AC, 48V, 5A, single phase, Optimized

ABLS1A48050

### Main

Range of product	Modicon Power Supply
Product or component type	Power supply
Power supply type	Regulated switch mode
Variant option	Optimized
Enclosure material	Metal
Nominal input voltage	100...240 V AC single phase 100...240 V AC phase to phase 140...375 V DC
Rated power in W	240 W
Output voltage	48 V DC
Power supply output current	5 A

### Complementary

Input voltage limits	85...264 V AC 120...375 V DC
Nominal network frequency	50...60 Hz
Network system compatibility	TN TT IT
Maximum leakage current	1 mA 240 V AC
Input protection type	Integrated fuse (not interchangeable) 6.3 A External protection (recommended) 20 A External protection (recommended) 6 A
Inrush current	30 A at 115 V 60 A at 230 V
Power factor	0.95 at 115 V AC 0.95 at 230 V AC
Efficiency	85 % at 115 V AC 88 % at 230 V AC
Output voltage adjustment	44...54 V
Power dissipation in W	36 W
Current consumption	< 2.8 A 115 V AC < 1.4 A 230 V AC < 2.4 A 140 V DC
Turn-on time	< 1 s
Holding time	> 20 ms 115 V AC > 20 ms 230 V AC
Startup with capacitive loads	8000 $\mu$ F

<b>Residual ripple</b>	200 mV
<b>Meantime between failure [MTBF]</b>	at 25 °C, full load conforming to SR 332
<b>Output protection type</b>	Against overload and short-circuits, protection technology: automatic reset Against over temperature, protection technology: manual reset Against overvoltage, protection technology: manual reset
<b>Connections - terminals</b>	Screw connection: 0.75...4 mm <sup>2</sup> , (AWG 18...AWG 12) without wire end ferrule for output Screw connection: 0.75...4 mm <sup>2</sup> , (AWG 18...AWG 12) with wire end ferrule for output Screw connection: 0.75...4 mm <sup>2</sup> , (AWG 18...AWG 12) without wire end ferrule for input Screw connection: 0.75...4 mm <sup>2</sup> , (AWG 18...AWG 12) with wire end ferrule for input
<b>Line and load regulation</b>	< 1.5 % at 0 to 100 % load at 25 °C < 0.5 % at full voltage range in line at 25 °C
<b>Status LED</b>	1 LED (green) output voltage
<b>Depth</b>	117.6 mm
<b>Height</b>	123.6 mm
<b>Width</b>	60 mm
<b>Product weight</b>	0.8 kg
<b>Output coupling</b>	Single/parallel by switch
<b>Marking</b>	CE UKCA
<b>Mounting support</b>	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 Double-profile DIN rail
<b>Supply</b>	SELV conforming to IEC 60950-1 SELV conforming to IEC 60204-1 SELV conforming to IEC 60364-4-41
<b>Dielectric strength</b>	3000 V AC with input to output 2000 V AC with input to ground 1500 V AC with output to ground
<b>Service life</b>	10 year(s) 40 °C 50 % load
<b>Overvoltage category</b>	II

## Environment

<b>Standards</b>	IEC 62368-1 EN/IEC 61204-3 IEC 61000-6-1 IEC 61000-6-2 IEC 61000-6-3 IEC 61000-6-4 IEC 61000-3-2 EN 61000-3-3 UL 62368-1 CSA C22.2 No 62368-1 CSA C22.2 No 107.1
<b>Product certifications</b>	CE CUL listed CUL recognized RCM CB Scheme EAC KC UKCA CURus
<b>Operating altitude</b>	< 5000 m overvoltage category II
<b>Shock resistance</b>	150 m/s <sup>2</sup> for 11 ms
<b>IP degree of protection</b>	IP20

<b>Ambient air temperature for operation</b>	-20...40 °C without derating mounting position A 115 V AC < 2000 m 40...70 °C with current derating mounting position A 115 V AC < 2000 m 40...70 °C with current derating of 1.67 % per °C mounting position A 115 V AC < 2000 m 50...70 °C with current derating of 2.5 % per °C mounting position A 230 V AC < 2000 m
<b>Electrical shock protection class</b>	Class I
<b>Pollution degree</b>	2
<b>Vibration resistance</b>	3 mm (f= 2...9 Hz) conforming to IEC 60068-2-6 10 m/s <sup>2</sup> (f= 9...200 Hz) conforming to IEC 60068-2-6
<b>Electromagnetic immunity</b>	Immunity to electrostatic discharge - test level: 8 kV (contact discharge) conforming to IEC 61000-4-2 Immunity to electrostatic discharge - test level: 15 kV (air discharge) conforming to IEC 61000-4-2 Immunity to conducted RF disturbances - test level: 15 V/m (80 MHz...2 GHz) conforming to IEC 61000-4-3 Immunity to conducted RF disturbances - test level: 5 V/m (2...2.7 GHz) conforming to IEC 61000-4-3 Immunity to conducted RF disturbances - test level: 5 V/m (2.7...6 GHz) conforming to IEC 61000-4-3 Immunity to fast transients - test level: 4 kV (on input-output) conforming to IEC 61000-4-4 Surge immunity test - test level: 4 kV (between power supply and earth) conforming to IEC 61000-4-5 Surge immunity test - test level: 3 kV (between phases) conforming to IEC 61000-4-5 Immunity to conducted RF disturbances - test level: 15 V (0.15...80 MHz) conforming to IEC 61000-4-6 Immunity to magnetic fields - test level: 30 A/m (50...60 Hz) conforming to IEC 61000-4-8 Immunity to voltage dips conforming to IEC 61000-4-11 Disturbing field emission conforming to EN 55016-2-3 Limits for harmonic current emissions conforming to IEC 61000-3-2 conforming to EN 55016-1-2 conforming to EN 55016-2-1
<b>Electromagnetic emission</b>	Conducted emissions conforming to IEC 61000-6-3 Radiated emissions conforming to IEC 61000-6-4

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	7.000 cm
<b>Package 1 Width</b>	17.500 cm
<b>Package 1 Length</b>	18.000 cm
<b>Package 1 Weight</b>	994.000 g
<b>Unit Type of Package 2</b>	S03
<b>Number of Units in Package 2</b>	9
<b>Package 2 Height</b>	30.000 cm
<b>Package 2 Width</b>	30.000 cm
<b>Package 2 Length</b>	40.000 cm
<b>Package 2 Weight</b>	9.592 kg



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	Yes
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	698d9b2a-7a6a-4b8f-a149-489156f55645
REACH Regulation	<a href="#">REACH Declaration</a>


## Use Again

### Repack and remanufacture

End of life manual availability	<a href="#">End of Life Information</a>
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

**Dimensions Drawings****Electrical Safety**


- If the unit is used in a manner not specified by the manufacturer, the protection provided by the equipment may be impaired.
- For means of disconnection a switch or circuit breaker, located near the product, must be included in the installation. A marking as disconnecting device for the product is required.
- The device has an internal fuse. The unit is tested and approved with branch circuit protective device up to 20A. This circuit breaker can be used as disconnecting device.
- The power supply is only suitable for audio, video, information, communication, industrial and control equipment.

**Dimensions****Front and Side Views**

## Connections and Schema


Connections and Schema

## Correct Parallel Connection



(1) : Load

## Incorrect Parallel Connection



(1) : Load

ABLx1Axxxxx-1 = ABLx1Axxxxx-2


max 2 x ABLx1Axxxxx

L1 = L2

ΔV max 25 mV

 $I_{Load} < 90\% 2 \times I_{nom}$ 

## Output Voltage Balancing



(1) :  $R_{\text{Load}1}$

(2) :  $R_{\text{Load}2}$

$R_{\text{Load}1} = R_{\text{Load}2}$

$I_1 = I_2 = \sim I_{\text{nom}}$

Connections and Schema


	(1)		
	<40°C	<50°C	<70°C
ABLS1A24021	50°C	60°C	75°C
ABLS1A24038	50°C	60°C	75°C
ABLS1A12062	50°C	60°C	80°C
ABLS1A24031	50°C	60°C	80°C
ABLS1A12100	60°C	70°C	90°C
ABLS1A24050	60°C	70°C	90°C
ABLS1A48025	60°C	70°C	90°C
ABLS1A24100	60°C	70°C	90°C
ABLS1A24200	95°C	95°C	90°C

(1) : Ambient


## Mounting and Clearance

Mounting





## Mounting Position A



## Mounting Position B




## Incorrect Mounting




## Performance Curves

## Performance Curve

## Mounting Position A



## Mounting Position B



X : Surrounding Air Temperature (°C)

Y : Percentage of Maximum Load (%)

1 : Altitude ≤ 2000 m (6561 ft), Input voltage = 230 VAC / 325 VDC

2 : Altitude ≤ 2000 m (6561 ft), 115 VAC / 162 VDC

3 : Altitude ≤ 5000 m (16404 ft), Input voltage = 230 VAC / 325 VDC

4 : Altitude ≤ 5000 m (16404 ft), 115 VAC / 162 VDC