

Product data sheet

Specifications



Thermal overload relay,Easy TeSys DPER,12-18A,class 10

DPER21

Product availability: Stock - Normally stocked in distribution facility

Main

Range	Easy TeSys
Product name	Easy TeSys DPER
Product or Component Type	Thermal overload relay
Device short name	DPER
Relay application	Overload protection
Product compatibility	Contactors DPE09-38
Thermal protection adjustment range	12...18 A
Thermal overload class	Class 10 IEC 60947-4-1
[Ui] rated insulation voltage	Power circuit 600 V cUL Power circuit 690 V IEC 60947-4-1

Complementary

Network type	DC AC
Network Frequency	0...400 Hz
Auxiliary contact composition	1 NO + 1 NC
[Ith] conventional free air thermal current	5 A signalling circuit
Permissible current	1.5 A 240 V AC-15 signalling circuit 0.1 A 250 V DC-13 signalling circuit
Phase failure sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Tripping threshold	1.14 +/- 0.06 Ir IEC 60947-4-1
Protection type	BS fuse 5 A - control circuit GB2 circuit breaker 5 A - control circuit GG fuse 5 A - control circuit
[Ue] rated operational voltage	690 V AC 0...400 Hz power circuit IEC 60947-4-1
[Uimp] rated impulse withstand voltage	6 kV
Surge withstand	6 kV IEC 60801-5
Dielectric strength	1.89 kV 50 Hz IEC 60947-1
Control type	Red push-button stop Blue push-button reset
Mounting support	Separate, with specific accessories Under contactor

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - terminals	Control circuit screw clamp terminals 2 0.002...0.004 in² (1...2.5 mm²) flexible without cable end Control circuit screw clamp terminals 2 0.002...0.004 in² (1...2.5 mm²) flexible with cable end Control circuit screw clamp terminals 2 0.002...0.004 in² (1...2.5 mm²) solid without cable end Power circuit screw clamp terminals 1 0.002...0.009 in² (1.5...6 mm²) flexible without cable end Power circuit screw clamp terminals 1 0.002...0.006 in² (1...4 mm²) flexible with cable end Power circuit screw clamp terminals 1 0.002...0.009 in² (1...6 mm²) solid without cable end
Tightening torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 22.1 lbf.in (2.5 N.m) screw clamp terminals
Height	2.6 in (66 mm)
Width	1.8 in (45 mm)
Depth	2.8 in (70 mm)
Net Weight	0.273 lb(US) (0.124 kg)

Environment

IP degree of protection	IP20 conforming to IEC 60529
Protective treatment	TH IEC 60068
Temperature compensation	-4...140 °F (-20...60 °C)
Ambient air temperature for operation	-4...140 °F (-20...60 °C) without derating IEC 60947-4-1
Ambient Air Temperature for Storage	-76...158 °F (-60...70 °C)
Shock resistance	15 gn 11 ms IEC 60068-2-7
Vibration resistance	6 gn on plate IEC 60068-2-6
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CUL
Product Certifications	cUL

Ordering and shipping details

Category	US10I1322363
Discount Schedule	0I13
GTIN	3606485332451
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	3.10 in (7.874 cm)
Package 1 Length	3.50 in (8.890 cm)
Package weight(Lbs)	4.640 oz (131.542 g)
Unit Type of Package 2	CAR

Number of Units in Package 2	24
Package 2 Height	6.00 in (15.240 cm)
Package 2 Width	12.50 in (31.750 cm)
Package 2 Length	16.00 in (40.640 cm)
Package 2 Weight	8.400 lb(US) (3.810 kg)

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	13
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
SCIP Number	224fb0ea-2bc1-482e-b6b4-c1bdd9779659
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Offer Marketing Illustration

Product benefits / Features



Easy TeSys Thermal Overload Relays

Range Accessories



Contact blocks



Auxiliary contact



Mounting accessories



Manual starter enclosure



Manual starter padlocking

Offer Marketing Illustration

Product benefits / Features

Easy TeSys

Thermal Overload Relays



Designed for the essential
Delivers the best balance between performance and budget without any compromise on quality



Easy choice and application
Easier to install, order and understand, and operate with multi-standard screws



Extended flexibility
Larger number of solutions covered with an extended product range



Offer Marketing Illustration

Product benefits / Features



The image shows a Schneider Easy TeSys Thermal Overload Relay, model LR10. It is a dark grey, rectangular device with three orange-colored screw terminals on top. The front panel features a 'STOP' button with a red indicator, a 'RESET' button, and a 'TRIP' indicator. The device is mounted on a terminal block with four terminals labeled 1, 2, 3, and 4. The background is a light green circle.

Easy TeSys Thermal Overload Relays


Technical Benefits

- Protecting A.C. circuits and motors from overloads, phase failure, long starting times, and prolonged stalled rotor conditions.
- Include automatic compensation for ambient temperature variations.
- 4 width sizes available to cover all ratings; from 45 mm (up to 38 A) to 242 mm (up to 630 A)
- Compensated relays with manual or automatic reset and relay trip indicator
- Terminal block for separate mounting

Image of product / Alternate images

Alternative





Technical Illustration

Assembly's dimensions

