

# Product data sheet

Specifications



3-phase control relay, Harmony Control Relays, 5A , 2NO, phase failure detection, 24..240V AC DC

RM35TM50MW

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Range of Product	Harmony Control Relays
Relay Type	Motor temperature control relay
Product or Component Type	Motor temperature control relay
Relay name	RM35TM
Relay monitored parameters	Phase sequence Motor temperature via PTC probe Phase failure detection
Measurement range	208...480 V AC 15...3100 Ohm
Time delay type	Without
Output contacts	2 NO
nominal output current	5 A
Contacts type and composition	2 NO
[Uc] control circuit voltage	24...240 V
Product Specific Application	For 3-phase supply

## Complementary

[Us] rated supply voltage	24...240 V AC/DC 50/60 Hz, non self-powered
Supply voltage limits	20.4...264 V AC 20.4...264 V DC
Reset time	10000 ms output
Maximum switching voltage	250 V AC 250 V DC
Switching capacity in VA	1250 VA
Minimum switching current	10 mA 5 V DC
Maximum switching current	5 A AC 5 A DC
Power consumption in VA	0...4 VA 24...240 V AC
Maximum power consumption in W	0.5 W DC
Control circuit frequency	50...60 Hz +/- 10 %
Resistance across terminals	602 mOhm
Measurement voltage limits	176...528 V AC
delay at power up	500 ms
Voltage range	176...528 V

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Response time</b>	> 50 ms (input Y1 (contact Y1-T1) and push-button)
<b>[Uc] control circuit voltage</b>	<= 3.6 V temperature control circuit T1-T2 terminals open)
<b>Short-circuit current</b>	0.007 A temperature sensing circuit T1-T2 terminals short circuited)
<b>Maximum resistance</b>	1500 Ohm temperature sensor 68 °F (20 °C)
<b>Tripping threshold</b>	3100 Ohm +/- 10 % temperature control circuit
<b>Reset threshold</b>	1650 Ohm +/- 10 % temperature control circuit
<b>Insulation resistance</b>	> 500 MOhm 500 V DC between supply and relay output IEC 60255-5 > 500 MOhm 500 V DC between measurement and relay output IEC 60664-1 > 1 MOhm 500 V DC between supply and measurement IEC 60255-5 > 500 MOhm 500 V DC between supply and relay output IEC 60664-1 > 500 MOhm 500 V DC between measurement and relay output IEC 60255-5 > 1 MOhm 500 V DC between supply and measurement IEC 60664-1
<b>[Ui] rated insulation voltage</b>	400 V IEC 60664-1
<b>Supply frequency</b>	50/60 Hz +/- 10 %
<b>Operating position</b>	Any position without derating
<b>Connections - terminals</b>	Screw terminals, 1 x 0.5...1 x 4 mm <sup>2</sup> AWG 20...AWG 11) solid without cable end Screw terminals, 2 x 0.5...2 x 2.5 mm <sup>2</sup> AWG 20...AWG 14) solid without cable end Screw terminals, 1 x 0.2...1 x 2.5 mm <sup>2</sup> AWG 24...AWG 12) flexible with cable end Screw terminals, 2 x 0.2...2 x 1.5 mm <sup>2</sup> AWG 24...AWG 16) flexible with cable end
<b>Tightening torque</b>	5.3...8.9 lbf.in (0.6...1 N.m) IEC 60947-1
<b>Housing material</b>	Self-extinguishing plastic
<b>Local signalling</b>	LED (green) for power ON LED (yellow) for phase of relay (R2) LED (yellow) for temperature of relay (R1)
<b>Mounting support</b>	35 mm symmetrical DIN rail conforming to IEC 60715
<b>Electrical durability</b>	10000 cycles
<b>Mechanical durability</b>	30000000 cycles
<b>Operating rate</b>	<= 360 operations/hour full load
<b>Utilisation category</b>	AC-12 IEC 60947-5-1 AC-13 IEC 60947-5-1 AC-14 IEC 60947-5-1 AC-15 IEC 60947-5-1 DC-12 IEC 60947-5-1 DC-13 IEC 60947-5-1
<b>Width</b>	1.4 in (35 mm)
<b>Product Weight</b>	0.29 lb(US) (0.13 kg)
<b>Control Type</b>	Without test button

## Environment

<b>Directives</b>	73/23/EEC - low voltage directive 89/336/EEC - electromagnetic compatibility
<b>Ambient Air Temperature for Storage</b>	-40...158 °F (-40...70 °C)
<b>Ambient air temperature for operation</b>	-4...122 °F (-20...50 °C)
<b>Relative humidity</b>	95 % 131 °F (55 °C) IEC 60068-2-30
<b>Vibration resistance</b>	0.35 mm (f= 5...57.6 Hz) conforming to IEC 60068-2-6 1 gn (f= 57.6...150 Hz) conforming to IEC 60255-21-1
<b>Shock resistance</b>	15 gn 11 ms IEC 60255-21-1
<b>IP degree of protection</b>	IP20 IEC 60529 terminals) IP30 IEC 60529 casing)
<b>Pollution degree</b>	3 IEC 60664-1
<b>Overvoltage category</b>	III conforming to IEC 60664-1
<b>Dielectric test voltage</b>	2 kV AC 50 Hz, 1 min
<b>Non-dissipating shock wave</b>	4 kV

## Ordering and shipping details

<b>Category</b>	US10CP222380
<b>Discount Schedule</b>	0CP2
<b>GTIN</b>	3389119405287
<b>Returnability</b>	Yes
<b>Country of origin</b>	ID

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Nbr. of units in pkg.</b>	1
<b>Package 1 Height</b>	1.69 in (4.300 cm)
<b>Package 1 Width</b>	3.07 in (7.800 cm)
<b>Package 1 Length</b>	3.74 in (9.500 cm)
<b>Package weight(Lbs)</b>	4.480 oz (127.000 g)
<b>Unit Type of Package 2</b>	S03
<b>Number of Units in Package 2</b>	48
<b>Package 2 Height</b>	11.81 in (30.000 cm)
<b>Package 2 Width</b>	11.81 in (30.000 cm)
<b>Package 2 Length</b>	15.75 in (40.000 cm)
<b>Package 2 Weight</b>	15.212 lb(US) (6.900 kg)

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle) **29**

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **Yes**

[EU RoHS Directive](#) **Pro-active compliance (Product out of EU RoHS legal scope)**

California proposition 65 **WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)**

## Use Again

### Repack and remanufacture


Circularity Profile [End of Life Information](#)

Take-back **No**

## Dimensions Drawings

3-Phase Supply and Motor Temperature Control Relays


## Dimensions and Mounting



## Connections and Schema

3-Phase Supply and Motor Temperature Control Relays



## Wiring Diagram



## Technical Description

Function Diagrams

**Phase Sequence Control and Phase Failure Detection (U measured < 0.7 x nominal supply voltage)**


**Motor Temperature Control via PTC Probe****Legend**

- Un Nominal 3-phase supply voltage
- R T1-T2 Resistance between terminals T1 and T2
- 11-14 R1 output relay connections
- Relay status: black color = energized.

**NOTE:** The temperature control relay can take up to 6 PTC (positive temperature coefficient) probes wired in series between terminals T1 and T2.

## Technical Illustration

## Dimensions




## Offer Marketing Illustration

## Product benefits / Features

## Technical Benefits

## Harmony Control Relay



## Offer Marketing Illustration

## Product benefits / Features

## Features

### Harmony Control Relay



**Wide monitoring parameters** (phase, current, voltage, liquid level, frequency, speed, temperature, and pump control) to meet your application needs.

**True RMS measurement** that minimizes the possibility of unexpected trips from highly polluted networks (except RM17TG and RM22TG)

**Experience** unprecedented accuracy, predictive maintenance, and superior security.

**Green Premium** labelled products, promising compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> product

**Compatible with a wide range of applications**, such as hoisting, packaging, lifts, textile, pumping, and water.

Image of product / Alternate images

Alternative

---





