

Product data sheet

Specifications



Auxiliary contact block, TeSys K,
1NO+1NC, front mounting, screw
clamp terminals

LA1KN11

Main

Range	TeSys
Product name	TeSys K
Product or component type	Auxiliary contact block
Device short name	LA1
Range compatibility	TeSys K LC1K TeSys K CA2K TeSys K CA3K TeSys K CA4K
Mounting location	Front
Pole contact composition	1 NO + 1 NC
Contacts operation	Instantaneous
[Ue] rated operational voltage	690 V AC 25...400 Hz
[Ui] rated insulation voltage	690 V conforming to IEC 60947-5-1 600 V conforming to UL 60947-5-1 600 V conforming to CSA C22.2 No 60947-5-1
[Ith] conventional free air thermal current	10 A (at 50 °C)
Standards	EN/IEC 60947-5-1 UL 60947-5-1 CSA C22.2 No 60947-5-1 GB/T 14048.5 JIS C8201-5-1 UL 60335-2-40:Annex JJ
Product certifications	CB Scheme CCC UL CSA CE UKCA

Complementary

Irms rated making capacity	110 A at <= 690 V AC conforming to IEC 60947
Permissible short-time rating	80 A 1 s 60 A 500 ms 110 A 100 ms
Associated fuse rating	10 A gG at <= 690 V conforming to IEC 60947
Minimum switching current	5 mA
Minimum switching voltage	17 V
Non overlap distance	0.5 mm
Insulation resistance	> 10 MΩ

Connections - terminals	Screw clamp terminals 1 cable(s) 0.34...1.5 mm ² flexible with cable end Screw clamp terminals 1 cable(s) 0.75...4 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 1.5...4 mm ² rigid Screw clamp terminals 2 cable(s) 0.34...1.5 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.75...4 mm ² flexible without cable end Screw clamp terminals 2 cable(s) 1.5...4 mm ² rigid
Tightening torque	1.3 N.m - with screwdriver Philips No 2 1.3 N.m - with screwdriver pozidriv No 2
Height	30 mm
Width	38 mm
Depth	35 mm
Product weight	0.045 kg

Environment

Environmental characteristic	Normal environment
IP degree of protection	IP20 conforming to IEC 60529
Protective treatment	TC conforming to IEC 60068
Ambient air temperature for storage	-50...80 °C
Ambient air temperature for operation	-25...50 °C
Operating altitude	2000 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.700 cm
Package 1 Width	4.000 cm
Package 1 Length	4.000 cm
Package 1 Weight	31.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5.000 cm
Package 2 Width	17.000 cm
Package 2 Length	17.000 cm
Package 2 Weight	316.000 g
Unit Type of Package 3	S02
Number of Units in Package 3	100
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	3.660 kg



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint 4

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic No

[EU RoHS Directive](#) Compliant

Use Again

Repack and remanufacture

End of life manual availability No need of specific recycling operations

Take-back No

WEEE Label  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins