

# Product data sheet

Specifications



Auxiliary contact, TeSys Ultra, 2NO, 690VAC/DC, for Start-stop signalling, Screw clamp terminals

LUA8E20

## Main

Range	TeSys
Device short name	LUA8
Product or component type	Auxiliary contact

## Complementary

Auxiliary contact composition	2 NO
Signalling function	Start-stop
[Ue] rated operational voltage	690 V AC 690 V DC
[Ith] conventional free air thermal current	5 A
Minimum switching voltage	17 V
minimum switching current	80 mA
Product weight	0.048 kg
Connections - terminals	Screw clamp terminals

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	11.0 cm
Package 1 Length	8.8 cm
Package 1 Weight	60.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	50
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.36 kg

## Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Compliant

## Use Again

### Repack and remanufacture

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins