

Product data sheet

Specifications



Regulated Power Supply, 380...500V AC, 48V, 10A, 3 phases, Universal

ABLU3A48100

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Modicon Power Supply
Product or Component Type	Power supply
Power supply type	Regulated switch mode
Variant option	Universal
Enclosure Material	Metal
Nominal input voltage	380...500 V AC three phase
Kw Rating	480 W
Output voltage	48 V DC
Power supply output current	10 A
Permissible temporary current boost	1.5 x In for 5 seconds)

Complementary

Efficiency at full load	320...575 V AC 3 phase
Nominal network frequency	50...60 Hz
Network system compatibility	TN TT IT
Maximum leakage current	2 mA 500 V AC
Input protection type	Integrated fuse (not interchangeable) 3.15 A External protection (recommended)
Inrush current	35 A 380 V 35 A 500 V
Power factor	0.90 at 380 V AC 0.88 at 500 V AC
Efficiency	92 % 380 V AC 92 % 500 V AC
Output voltage adjustment	48...56 V
Power dissipation in W	33 W
Current consumption	< 0.85 A 380 V AC < 0.73 A 500 V AC
Turn-on time	< 1 s
Holding time	> 20 ms 380 V AC > 20 ms 500 V AC
Startup with capacitive loads	200000 μ F
Residual ripple	< 150 mV

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Meantime between failure [MTBF]	890200 h at 77 °F (25 °C), full load conforming to SR 332 346200 h at 131 °F (55 °C), 80 % load conforming to SR 332
Output protection type	Against overload and short-circuits, protection technology: manual or automatic reset by switch Against over temperature, protection technology: automatic reset Against overvoltage, protection technology: manual reset
Connections - terminals	Screw connection 4...6 mm ² , AWG 12...AWG 10) without wire end ferrule output Screw connection 4 mm ² , AWG 12) with wire end ferrule output Screw connection 0.75...6 mm ² , AWG 18...AWG 10) without wire end ferrule input Screw connection 0.75...4 mm ² , AWG 18...AWG 12) with wire end ferrule input Cage clamp 0.2...1.5 mm ² , AWG 22...AWG 16) without wire end ferrule diagnostic relay Cage clamp 0.2...0.75 mm ² , AWG 22...AWG 18) with wire end ferrule diagnostic relay Cage clamp 0.2...0.75 mm ² , AWG 22...AWG 18) with wire end ferrule shut down input
Line and load regulation	< 0.17 % network 100 % load in line at 77 °F (25 °C) < 0.6 % +/- 0.5 % network 150 % load at 77 °F (25 °C)
Status LED	1 LED (green and red) product status
Depth	5.008 in (127.2 mm)
Height	4.9 in (124 mm)
Width	2.6 in (65 mm)
Product Weight	2.54 lb(US) (1.15 kg)
Output coupling	Parallel
Marking	CE UKCA
Mounting support	Top hat type TH35-15 rail IEC 60715 Top hat type TH35-7.5 rail IEC 60715 Double-profile DIN rail
Supply	SELV IEC 60950-1 SELV IEC 60204-1 SELV IEC 60364-4-41
Dielectric strength	4000 V AC with input to output 2000 V AC with input to ground 1500 V AC with output to ground 4000 V AC with input to diagnostic relay 500 V AC with output to diagnostic relay 1500 V AC with diagnostic relay to ground with shutdown input not isolated from output
Diagnostic relay	Electromechanical relay 1000.0 mA 30 V
Service life	10 year(s) 104 °F (40 °C) 80 % load
Overvoltage category	III II

Environment

Standards	IEC 62368-1 EN/IEC 61204-3 IEC 61000-6-1 IEC 61000-6-2 IEC 61000-6-3 IEC 61000-6-4 IEC 61000-3-2 EN 61000-3-3 UL 62368-1 CSA C22.2 No 62368-1 CSA C22.2 No. 107.1
------------------	---

Product certifications	CE CUL Listed CUL Recognized RCM CB Scheme EAC KC UKCA CURus
Operating altitude	< 5000 m overvoltage category III overvoltage category II
Shock resistance	150 m/s ² 11 ms
IP degree of protection	IP20
Ambient air temperature for operation	-13...131 °F (-25...55 °C) without current derating mounting position A < 6561.68 ft (2000 m) 131...158 °F (55...70 °C) with current derating of 3.3 % per °C mounting position A < 6561.68 ft (2000 m)
Electrical shock protection class	Class I
Pollution degree	2
Vibration resistance	3.5 mm (f= 3...11.9 Hz) conforming to IEC 60068-2-6 20 m/s ² (f= 11.9...150 Hz) conforming to IEC 60068-2-6
Electromagnetic immunity	Immunity to electrostatic discharge - test level: 8 kV (contact discharge) conforming to IEC 61000-4-2 Immunity to electrostatic discharge - test level: 15 kV (air discharge) conforming to IEC 61000-4-2 Immunity to conducted RF disturbances - test level: 15 V/m (80 MHz...2 GHz) conforming to IEC 61000-4-3 Immunity to conducted RF disturbances - test level: 5 V/m (2...2.7 GHz) conforming to IEC 61000-4-3 Immunity to conducted RF disturbances - test level: 5 V/m (2.7...6 GHz) conforming to IEC 61000-4-3 Immunity to fast transients - test level: 4 kV (on input-output) conforming to IEC 61000-4-4 Surge immunity test - test level: 4 kV (between power supply and earth) conforming to IEC 61000-4-5 Surge immunity test - test level: 3 kV (between phases) conforming to IEC 61000-4-5 Immunity to conducted RF disturbances - test level: 15 V (0.15...80 MHz) conforming to IEC 61000-4-6 Immunity to magnetic fields - test level: 30 A/m (50...60 Hz) conforming to IEC 61000-4-8 Immunity to voltage dips conforming to IEC 61000-4-11 Disturbing field emission conforming to EN 55016-2-3 Limits for harmonic current emissions conforming to IEC 61000-3-2 conforming to EN 55016-1-2 conforming to EN 55016-2-1
Electromagnetic emission	Conducted emissions IEC 61000-6-3 Radiated emissions IEC 61000-6-4

Ordering and shipping details

Category	US1CP1222524
Discount Schedule	CP12
GTIN	3606482185265
Returnability	Yes
Country of origin	TH

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	3.72 in (9.45 cm)

Package 1 Width	6.97 in (17.7 cm)
Package 1 Length	7.36 in (18.7 cm)
Package weight(Lbs)	3.333 lb(US) (1.512 kg)
Unit Type of Package 2	S03
Number of Units in Package 2	7
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	24.7 lb(US) (11.2 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

REACH Regulation

[REACH Declaration](#)

Use Again

Repack and remanufacture

Circularity Profile

[End of Life Information](#)

Take-back


No

WEEE Label


 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.


Dimensions Drawings

Dimensions



Connections and Schema

Wiring


Block Diagram

- (1) : Input
- (2) : EMI filter
- (3) : Relay control
- (4) : Interleave PFC converter
- (5) : Primary control
- (6) : Main LLC converter
- (7) : PFC controller
- (8) : Primary AUX
- (9) : Synchronous rectifier
- (10) : SR controller
- (11) : CV & CC feedback
- (12) : Secondary MCU
- (13) : Secondary AUX
- (14) : Output filter
- (15) : Automanual switch
- (16) : LED control


Mounting and Clearance

Mounting


Mounting Position



Incorrect Mounting




Performance Curves

Performance Curve

X : Surrounding Air Temperature (°C)

Y : Percentage of Maximum Load (%)

Overvoltage Protection Behavior



Overvoltage range : 54...60 VDC, Latch mode

(1) : Variable output voltage range

(2) : Latch

(3) : Typical overvoltage condition as seen at the output

(4) : Maximum overvoltage protection level

(5) : Overvoltage protection

(6) : Normal output voltage

(7) : Zero output