

Product data sheet

Specifications



Blanking plug, Harmony XB5, plastic, black, for 22mm hole

ZB5SZ3

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony XB5 Harmony XB4
Accessory / Separate Part Type	Blanking plug
Accessory / separate part category	Installation accessories
Product or Component Type	Blanking plug
Accessory / separate part destination	Ø 22 mm cut-outs for circular heads
Cap/operator or lens colour	Dark grey

Complementary

Material	Plastic
Bezel material	Dark grey plastic
Head type	Standard
Colour	Dark grey
Device Composition	Nut Blanking plug
Sale per indivisible quantity	10
Product Weight	0.020 lb(US) (0.009 kg)
Shape of signaling unit head	Round
Operator profile	Flush
Station name	XALD 2...5 cut-outs XALK 2...5 cut-outs

Environment

NEMA degree of protection	NEMA 13 NEMA 4X
IP degree of protection	IP66 IEC 60529 IP67 IP69 IP69K
IK degree of protection	IK03 conforming to IEC 50102
Standards	JIS C8201-5-1 EN/IEC 60947-1 EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60947-5-4 UL 508 JIS C8201-1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10CS222469
Discount Schedule	0CS2
GTIN	3389110099522
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.98 in (2.500 cm)
Package 1 Width	1.18 in (3.000 cm)
Package 1 Length	1.18 in (3.000 cm)
Package weight(Lbs)	0.317 oz (9.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	3.54 in (9.000 cm)
Package 2 Width	2.76 in (7.000 cm)
Package 2 Length	2.76 in (7.000 cm)
Package 2 Weight	3.386 oz (96.000 g)
Unit Type of Package 3	S03
Number of Units in Package 3	400
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	9.480 lb(US) (4.300 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	1
--	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
--	-----

Packaging without single use plastic	Yes
--------------------------------------	-----

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-----------------------------------	--

California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
---------------------------	---

Use Again

Repack and remanufacture

Take-back	No
-----------	----

Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony XB5

Conformity with IEC, UL, CSA, CCC EAC, and JIS standards, as well as CE marking and marine approvals



Operating temperature from -40°C to 70°C

Up to IP66, 67, 69, 69K, and type 4X protection ratings



Shock protection level up to IK06

High vibration resistance with shake-proof terminal screws

Secure switching of inductive or heavy DC loads directly – 100 000 operations at 10A, 24V dc

Offer Marketing Illustration

Product benefits / Features

Features

Harmony XB5



-  Quick and easy assembly and disassembly
-  Excellent mechanical connection with operator head
-  Various types of connection: screw clamp, connector, Faston connector, spring terminal, or printed circuit board
-  Large set of accessories to customize your panels
-  Robustness to withstand harsh environments

Image of product / Alternate images

Alternative





