

Product data sheet

Specifications



Long terminal shields, TeSys GV5 / GV7, 3P, IP40, pole pitch 35 mm

GV7AC01

Main

Range	TeSys
Product or component type	Long terminal shield
Device short name	GV7AC
Range compatibility	TeSys TeSys GV5 motor circuit breaker TeSys TeSys GV7 motor circuit breaker
Accessory / separate part category	Insulation accessories

Complementary

IP degree of protection	IP40
Quantity per set	Set of 1
Product weight	0.145 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	9.000 cm
Package 1 Length	12.900 cm
Package 1 Weight	150.000 g
Unit Type of Package 2	S04
Number of Units in Package 2	24
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	4.244 kg
Unit Type of Package 3	P06
Number of Units in Package 3	96
Package 3 Height	74.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	25.000 kg

Contractual warranty

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
California proposition 65	<p>WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov</p>



Use Again

Repack and remanufacture

Take-back	No
WEEE Label	<p> The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins</p>

Dimensions Drawings

Motor Circuit Breakers with Terminal Shields or Phase Barriers GV7R + GV7AC01 or AC04



(2) Phase barriers: GV7AC04.
(3) Terminal shields: GV7AC01.