

# Product data sheet

Specifications



## Contact block, Harmony XAC, single contact, spring return, emergency stop push button, 3NO

XENT1991

**Product availability: Non-Stock - Not normally stocked in distribution facility**

### Main

Range of Product	Harmony XAC
Product or Component Type	Contact block
Component name	XENT
Electrical circuit type	Control circuit Power circuit
Contact block application	Emergency stop push-button
Contact block type	Single
Type of operator	Spring return
Product Compatibility	XACD
Contacts type and composition	3 NC
Contact operation	Slow-break

### Complementary

Connections - terminals	Screw clamp terminals, 1 x 2.5 mm <sup>2</sup> with or without cable end Screw clamp terminals, 2 x 1.5 mm <sup>2</sup> with or without cable end
Mechanical durability	3000000 cycles
[I <sub>the</sub> ] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	400 V 3)IEC 60947-1
[Ui <sub>imp</sub> ] rated impulse withstand voltage	4 kV IEC 60947-1
Short-circuit protection	6 A fuse protection cartridge aM
Rated operational power in W	3000 W AC-23B 400 V
Terminals description ISO n°1	(31-32)NC (11-12)NC (21-22)NC
Product Weight	0.09 lb(US) (0.04 kg)

### Environment

Standards	IEC 60947-5-1 UL 508 CSA C22.2 No 14
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Vibration resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	70 gn IEC 60068-2-27

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

Overvoltage category	Class II conforming to IEC 61140
----------------------	----------------------------------

## Ordering and shipping details

---

Category	US10CS222466
Discount Schedule	0CS2
GTIN	3389110609103
Returnability	Yes
Country of origin	FR

## Packing Units

---

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.42 in (3.6 cm)
Package 1 Width	2.09 in (5.3 cm)
Package 1 Length	2.32 in (5.9 cm)
Package weight(Lbs)	1.5 oz (42.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	30
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	3.223 lb(US) (1.462 kg)

## Contractual warranty

---

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	<b>WARNING:</b> This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>

## Use Again

### Repack and remanufacture

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.