

# Product data sheet

Specifications

## Additional neutral block,TeSys Control,175A,for V5 / V6



VZ13

### Main

Range	TeSys
Device short name	VZ
Product or component type	Additional neutral block
Performance level	High performance
Poles description	1N
Contacts type and composition	1 NO
Contact operation	Early make, late break
Product compatibility	V5 V6
Range compatibility	TeSys TeSys VARIO switch disconnector
Network type	AC DC
Network frequency	50/60 Hz

### Complementary

Mounting location	Left Right
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uiimp] rated impulse withstand voltage	6 kV
[Ith] conventional free air thermal current	175 A
Mechanical durability	30000 cycles
Electrical durability	30000 cycles DC-1...5 30000 cycles AC-21
Connections - terminals	Screw clamp terminals 70 mm <sup>2</sup> - flexible - with cable end Screw clamp terminals 95 mm <sup>2</sup> - solid
Tightening torque	22.6 N.m - on screw clamp terminals
Height	125 mm
Width	30 mm
Depth	63 mm
Product weight	0.25 kg

### Environment

Standards	IEC 60947-3
-----------	-------------

<b>Product certifications</b>	UL CSA GL UKCA
<b>Protective treatment</b>	TC
<b>IP degree of protection</b>	IP20 conforming to IEC 60529
<b>Mechanical robustness</b>	Vibrations 10...150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (15 gn) conforming to IEC 60068-2-27
<b>Ambient air temperature for operation</b>	-20...50 °C
<b>Fire resistance</b>	960 °C conforming to IEC 60695-2-1

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	7.500 cm
<b>Package 1 Width</b>	7.000 cm
<b>Package 1 Length</b>	12.000 cm
<b>Package 1 Weight</b>	256.000 g
<b>Unit Type of Package 2</b>	S03
<b>Number of Units in Package 2</b>	30
<b>Package 2 Height</b>	30.000 cm
<b>Package 2 Width</b>	30.000 cm
<b>Package 2 Length</b>	40.000 cm
<b>Package 2 Weight</b>	8.190 kg

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Environmental footprint

Total lifecycle Carbon footprint **1**

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant with Exemptions**

SCIP Number **E8ec339b-85c3-4216-bd7f-79794a93ade1**

REACH Regulation [REACH Declaration](#)

PVC free **Yes**

## Use Again

### Repack and remanufacture

End of life manual availability **No need of specific recycling operations**

Take-back **No**

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Technical Illustration

### Assembly's dimensions

---

