

Product data sheet

Specifications



slim interface relay, Harmony
Electromechanical Relays, pre
assembled, 6A, 1CO, with LED,
screw connec to rs, 48V AC/DC

RSL1PVEU

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony Electromechanical Relays
Series name	RSL series
Product or Component Type	Pre-assembled plug-in relay with socket
Relay Type	Slim interface relay
Contact operation	Standard
Contacts type and composition	1 C/O
Status LED	With
[Uc] control circuit voltage	48 V AC/DC
[Ite] conventional enclosed thermal current	6 A -40...131 °F (-40...55 °C)

Complementary

Fixing Mode	Plastic compression spring
Average resistance	10600 Ohm DC 23 °C +/- 10 %
[Uiimp] rated impulse withstand voltage	6 kV IEC
[Ie] rated operational current	6 A 1 C/O AC-1/DC-1)IEC/UL
minimum switching current	100 mA
Minimum switching voltage	12 V
[Ui] rated insulation voltage	250 V IEC 277 V cUL
Minimum switching capacity	120 mW
Maximum switching voltage	277 V
Drop-out voltage threshold	>= 0.05 Uc
Load current	6 A 250 V AC 0.5 mm mounting distance
Electrical durability	60000 cycles resistive, 6 A 250 V, AC-1
Maximum switching capacity	1500 VA 150 W
Operating time	5 ms reset 12 ms
Terminals description ISO n°1	(11-12-14)OC (A1-A2)CO
Average coil consumption	0.17 W, DC
Mechanical durability	10000000 cycles

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Safety reliability data	B10d = 60000
Operating rate	<= 72000 cycles/hour no-load <= 360 cycles/hour under load
Tightening torque	< 0.5 N.m M2.5
Control Type	Without lockable test button
Compatibility code	RSL
Contact terminal arrangement	Separate
Connections - terminals	Screw connectors, 1 x 0.2...1 x 2.5 mm ² AWG 24...AWG 14) flexible with cable end Screw connectors, 1 x 0.2...1 x 2.5 mm ² AWG 24...AWG 14) solid without cable end
Protection category	RT III
Mounting Support	35 mm symmetrical DIN rail
Operating position	Any position
Test levels	Level A group mounting
Device presentation	Complete product
Sale per indivisible quantity	10
Contacts material	Silver alloy (AgSnO2)
Shape of pin	Flat (PCB type)
Width	0.2 in (6.2 mm)
Height	3.09 in (78.6 mm)
Depth	3.7 in (95 mm)
Product Weight	0.064 lb(US) (0.029 kg)

Environment

Input voltage	48 V AC/DC 43.2...57.6 V)
Dielectric strength	1000 V AC between contacts 4000 V AC between coil and contact
IP degree of protection	IP40 conforming to IEC 60529
Ambient air temperature for operation	-40...131 °F (-40...55 °C)
Standards	CSA C22.2 No 14 UL 508 IEC 61810-1
Product Certifications	GOST CSA UL
Marking	CE
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Vibration resistance	10 gn +/- 1 mm 10...150 Hz)10 cycles not operating IEC 60068-2-6 5 gn +/- 1 mm 10...150 Hz)10 cycles in operation IEC 60068-2-6
Shock resistance	10 gn 11 ms) in operation IEC 60068-2-27 5 gn 11 ms) not operating IEC 60068-2-27

Ordering and shipping details

Category	US10CP221127
Discount Schedule	OCP2
GTIN	3606480077845

Returnability	Yes
---------------	-----

Country of origin	CN
-------------------	----

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Nbr. of units in pkg.	1
-----------------------	---

Package 1 Height	0.28 in (0.7 cm)
------------------	------------------

Package 1 Width	3.11 in (7.9 cm)
-----------------	------------------

Package 1 Length	3.78 in (9.6 cm)
------------------	------------------

Package weight(Lbs)	1.0 oz (28 g)
---------------------	---------------

Unit Type of Package 2	BB1
------------------------	-----

Number of Units in Package 2	10
------------------------------	----

Package 2 Height	2.76 in (7 cm)
------------------	----------------

Package 2 Width	4.06 in (10.3 cm)
-----------------	-------------------

Package 2 Length	3.35 in (8.5 cm)
------------------	------------------

Package 2 Weight	10.9 oz (310 g)
------------------	-----------------

Unit Type of Package 3	S03
------------------------	-----

Number of Units in Package 3	300
------------------------------	-----

Package 3 Height	11.81 in (30 cm)
------------------	------------------

Package 3 Width	11.81 in (30 cm)
-----------------	------------------

Package 3 Length	15.75 in (40 cm)
------------------	------------------

Package 3 Weight	21.711 lb(US) (9.848 kg)
------------------	--------------------------

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)

5

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

California proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again


Repack and remanufacture

Take-back

No

Dimensions Drawings

Dimensions



Technical Illustration

Dimensions




Image of product / Alternate images

Alternative

