

Product data sheet

Specifications



Communication module, TeSys
Ultra, 24VDC, 0 to 500mA, Advantys
STB, front side

LULC15

Main

Range	TeSys
Device short name	LUL
Product or component type	Communication module
Product compatibility	LUCC LUCA LUCL LUCM LUCB LUCD
Device application	Communication
Range compatibility	TeSys TeSys U LUB non reversing power base TeSys TeSys U LU2B reversing power base

Complementary

main function available	Communication module
Mounting mode	Plug-in
Mounting location	Front side
Physical interface	CAN
Bus type	Advantys STB
Cable connector type	Fire wire
Communication port protocol	CAN2.B CAN2.0A
Addressing	Self-addressing
Transmission rate	800 kbit/s
Current consumption	1.5 mA at 24 V DC 20...28 V
Logic input	Positive at 24 V DC - 7 mA
Response time	10 ms +/- 30 % change to state 0 10 ms +/- 30 % change to state 1
Input type	Resistive
Number of outputs	2 dedicated to starter-controller coil operation 1
[Us] rated supply voltage	24 V DC
Output current	<= 500 mA
Switching current capacity	0.5 mA at 24 V
Local signalling	3 LEDs front panel
Connection pitch	3.81 mm

Connections - terminals	Screw clamp terminals 1 cable(s) 0.14...1 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 0.14...1 mm ² rigid without cable end Screw clamp terminals 1 cable(s) 0.25...0.5 mm ² flexible with cable end Screw clamp terminals 1 cable(s) 0.25...1 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.14...0.5 mm ² rigid without cable end Screw clamp terminals 2 cable(s) 0.14...0.75 mm ² flexible without cable end Screw clamp terminals 2 cable(s) 0.25...0.34 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.5 mm ² flexible with cable end
--------------------------------	---

Associated cable type	AWG 26...AWG 16
------------------------------	-----------------

Tightening torque	0.2...0.25 N.m2.5 mm
--------------------------	----------------------

Environment

Ambient air temperature for operation	-25...55 °C
--	-------------

IP degree of protection	IP20 conforming to IEC 60529
--------------------------------	------------------------------

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Number of Units in Package 1	1
-------------------------------------	---

Package 1 Height	4.9 cm
-------------------------	--------

Package 1 Width	4.9 cm
------------------------	--------

Package 1 Length	11.3 cm
-------------------------	---------

Package 1 Weight	106.0 g
-------------------------	---------

Unit Type of Package 2	S02
-------------------------------	-----

Number of Units in Package 2	35
-------------------------------------	----

Package 2 Height	15.0 cm
-------------------------	---------

Package 2 Width	30.0 cm
------------------------	---------

Package 2 Length	40.0 cm
-------------------------	---------

Package 2 Weight	4.065 kg
-------------------------	----------

Contractual warranty

Warranty	18 months
-----------------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	E383808a-7832-4e0a-8697-e499929809d4
Halogen-free status	Halogen free plastic parts product

Use Again

Repack and remanufacture

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins