

Product data sheet

Specifications



Remote control, Harmony eXLhoist,
compact, LED, 6 motion push
buttons, 2 auxiliary push buttons

ZART8LS

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Range of Product	Harmony eXLhoist
Product or Component Type	Hand-held remote control
Device short name	ZART
Control Button Type	6 configurable motion push-button 2 configurable auxiliary push-button

Complementary

Material	Protective cover EPDM rubber Push-button cover polyurethane Enclosure ABS + PC
Display type	5 LEDs
Operating Distance	50 m
Communication network type	Wireless Zigbee
Transmission frequency	2.4 GHz
Maximum sensing distance	328.08 ft (100 m) in free field
Response time	< 500 ms simplex
Charging time	10800 s 0 s
Autonomy	150 h Li-Ion (Lithium Ion) 100 h
Mechanical durability	1000000 cycles
Width	3.3 in (85 mm)
Height	7.6 in (193 mm)
Depth	1.7 in (43 mm)
Product Weight	0.7 lb(US) (0.3 kg)

Environment

Radio agreement	IC FCC
IP degree of protection	IP65
Ambient Air Temperature for Operation	-4...131 °F (-20...55 °C)
Ambient Air Temperature for Storage	-4...113 °F (-20...45 °C)
Operating altitude	0...6561.68 ft (0...2000 m)
Storage altitude	0...9842.5 ft (0...3000 m)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Relative humidity	0...95 % -4...140 °F (-20...60 °C) operating
Product Certifications	CE

Ordering and shipping details

Category	US10CS222479
Discount Schedule	OCS2
GTIN	3606481389107
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.09 in (5.3 cm)
Package 1 Width	4.13 in (10.5 cm)
Package 1 Length	8.46 in (21.5 cm)
Package weight(Lbs)	14.9 oz (423.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	18
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	17.829 lb(US) (8.087 kg)



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO₂ eq, Total Life cycle) **15**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **Yes**

[EU RoHS Directive](#) **Pro-active compliance (Product out of EU RoHS legal scope)**

SCIP Number **6e438e59-42d1-4633-bfe2-cb5ef607659b**

California proposition 65 **WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)**

Use Again

Repack and remanufacture


Circularity Profile [End of Life Information](#)

Take-back **No**

WEEE Label  **The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.**


Dimensions Drawings

Dimensions



Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features

Technical benefits

ZAR Harmony Pocket remote

The Harmony Pocket Remote uses the worldwide free 2.4 GHz frequency to allow unrestricted operation.

Product certifications:
CE, UL
Radio certifications:
FCC, IC

Users can integrate 3, 4, 6, 8 or 10 buttons according to their needs

IP 67 for the transmitter and IP 66 for the receiver



Image of product / Alternate images

Alternative







Image of product in real life situation

