

# Product data sheet

Specifications



## braking resistor, Altivar, 60Ohms, 0.16kW, IP20

VW3A7731

**Product availability: Non-Stock - Not normally stocked in distribution facility**

### Main

Range of Product	Altivar
Range Compatibility	Altivar Machine ATV320 Altivar Machine ATV340 Easy Altivar 310 Altivar Process ATV900 Easy Altivar 310L
Product or Component Type	Braking resistor
Ohmic value	60 Ohm

### Complementary

Product compatibility	Variable speed drive ATV930 wall mount 5.5 kW 380...480 V light cycle Variable speed drive ATV930 wall mount 7.5 kW 380...480 V light cycle Variable speed drive ATV930 wall mount 1.5 kW 200...240 V light cycle Variable speed drive ATV930 wall mount 2.2 kW 200...240 V light cycle Variable speed drive ATV950 wall mount 5.5 kW 380...480 V light cycle Variable speed drive ATV950 wall mount 7.5 kW 380...480 V light cycle Variable speed drive ATV930 wall mount 1.5 kW 200...240 V medium cycle Variable speed drive ATV930 wall mount 2.2 kW 200...240 V medium cycle Variable speed drive ATV340 4 kW 380...480 V light cycle Variable speed drive ATV340 5.5 kW 380...480 V light cycle Variable speed drive ATV320 0.55 kW 200...240 V Variable speed drive ATV320 0.75 kW 200...240 V Variable speed drive ATV320 1.1 kW 200...240 V Variable speed drive ATV320 1.5 kW 200...240 V Variable speed drive ATV320 4 kW 380...480 V Variable speed drive ATV320 5.5 kW 380...480 V Variable speed drive ATV310 5.5 kW Variable speed drive ATV310 7.5 kW Variable speed drive ATV930 7.5 kW 500...690 V light cycle Variable speed drive ATV930 11 kW 500...690 V light cycle Variable speed drive ATV930 10 hp 600 V light cycle Variable speed drive ATV930 15 hp 600 V light cycle Variable speed drive ATV320 5.5 kW 525...600 V Variable speed drive ATV310L 0.75 kW Variable speed drive ATV310L 1.5 kW Variable speed drive ATV310L 2.2 kW Variable speed drive ATV310L 3.0 kW Variable speed drive ATV310L 4.0 kW Variable speed drive ATV310L 5.5 kW
Duty cycle	Light cycle (heavy duty) <0.8 s braking with 150 % braking torque for a 40 s cycle Light cycle (normal duty) <0.8 s braking with 120 % braking torque for a 40 s cycle Medium cycle (normal duty) <4 s braking with 135 % braking torque for a 40 s cycle Medium cycle (heavy duty) <4 s braking with 165 % braking torque for a 40 s cycle
Average power available	0.16 kW 122 °F (50 °C)
Electrical connection	terminal <= 10 mm <sup>2</sup> / AWG 8 drive
Protection type	Thermal protection via drive
Width	4.1 in (105 mm)
Height	13.6 in (345 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Depth	3.9 in (100 mm)
Product Weight	4.0 lb(US) (1.8 kg)

## Environment

IP Degree of Protection	IP20
Ambient Air Temperature for Storage	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Operation	32...122 °F (0...50 °C)

## Ordering and shipping details

Category	US1CP4E22209
Discount Schedule	CP4E
GTIN	3606480802256
Returnability	Yes
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	4.72 in (12.000 cm)
Package 1 Width	6.69 in (17.000 cm)
Package 1 Length	14.17 in (36.000 cm)
Package weight(Lbs)	4.522 lb(US) (2.051 kg)
Unit Type of Package 2	P06
Number of Units in Package 2	30
Package 2 Height	29.53 in (75.000 cm)
Package 2 Width	23.62 in (60.000 cm)
Package 2 Length	31.50 in (80.000 cm)
Package 2 Weight	154.324 lb(US) (70.000 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	<b>WARNING:</b> This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Use Again


### Repack and remanufacture

Take-back	No
-----------	----

## Dimensions Drawings

## Dimensions

## Right Side and Front View



## Dimensions in mm

A	B	C	A1	C1	$\emptyset$
105	100	345	72	316	4.5

## Dimensions in in.


A	B	C	A1	C1	$\emptyset$
4.13	3.94	13.58	2.83	12.44	0.18

## Mounting and Clearance


Mounting and Clearance

(1) Braking resistor

mm  
in.




## Connections and Schema

Recommended Schema**1 Braking Resistor**

**A1** : Drive or external braking unit

**A2** : Braking resistor

**PA, PB** : Bus DC

**2 Braking Resistors**

**A1** : Drive or external braking unit

**A2** : Braking resistor

**PA, PB** : Bus DC