

Product data sheet

Characteristics

8910DP32V14

Contactor, Definite Purpose, 30A, 2 pole, 24/24 VAC 50/60 Hz coil, open



Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	30 A
Number of Poles	2P
Pole contact composition	2 NO
Range of Product	DP

Complementary

Maximum Horse Power Rating	2 Hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Locked rotor rated current	125 A 460 V AC 100 A 575 V AC 150 A 277 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	24 V AC 50/60 Hz
Phase	1 phase
Electrical Connection	Binder head Quick connect terminals

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	21356-8910 DP 32
Discount Schedule	CP1B
GTIN	785901080442
Nbr. of units in pkg.	1
Package weight(Lbs)	9.76 oz (276.691 g)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.10 in (5.334 cm)
Package 1 width	2.70 in (6.858 cm)
Package 1 Length	3.60 in (9.144 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Weight	7.55 lb(US) (3.425 kg)
Package 2 Height	5.80 in (14.732 cm)
Package 2 width	7.00 in (17.78 cm)
Package 2 Length	7.50 in (19.05 cm)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------